

15 kV Class Elbow Arrester (5.1 kV MCOV)

By Hubbell Power Systems
Catalog # [215ELA06](#)

Deadfront Elbow Arrester, 15kV 5.1 MCOV

Features

- Meets or Exceeds IEEE Std. 386 and IEEE Std. C62.11. Section 8.1 requirements
- Interchangeable with other products meeting the same requirements
- Fully shielded, insulated and submersible

General

Catalog Number	215ELA06
EU RoHS Indicator	No
Grounding Style	36 in Line Lead
Material	Polymer
Type	Underground Arresters
UPC	096359360551

Dimensions

Height	6.6 in
Maximum Operating Altitude	6000 ft
Weight	3.7 lb

Electrical Ratings

Duty Cycle	6 kV
MCOV	5.1 kV
Maximum Discharge Voltage	• 19.5 kV @ 1.5 kA • 20.5 kV @ 3 kA • 22 kV @ 5 kA



- 24.5 kV @ 10 kA
- 28.5 kV @ 20 kA
- 37 kV @ 40 kA

Maximum Switching Surge Protective Level @ 500A kV Class	17 kV 15 kV
--	----------------

Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
--------------------------	----------------------

Logistics

Pallet Quantity	160
Standard Package	1

Product Assets

- [Catalogs - Cable Accessories](#)
- [Catalogs - Underground Arresters](#)
- [Installation Manuals - Elbow Arrester Installation and Operation Instructions](#)
- [Literature - Application Guide: Metal-oxide Surge Arresters for use on AC systems](#)
- [Sales Drawings - 15 kV, 200A Loadbreak Elbow Arrester](#)
- [Specifications - 215ELA06](#)
- [Video - Hubbell Power Systems Elbow Arrester](#)
- [Video - Hubbell Power Systems Metal Oxide Varistor](#)
- [Video - Grease Best PRactices](#)