

## 15 kV, Load Break Elbow w/ ProbeLok Bimetal Contact, Shield Adapter Kit

By Hubbell Power Systems  
Catalog # 215LE32PS

Load Break Elbow, 200 Amp, 15 kV, Long ProbeLok Bimetal Contact, Shield Adapter Kit, Cable Insulation Diameter range = 0.495 - 0.730 inches, #2 or #3 Solid or Compacted and #3 or #4 Stranded or Compressed



\*Representative Image

### Features

- Meets or Exceeds IEEE Std. 386 and IEEE Std. 592 requirements
- Interchangeable with other products meeting the same requirements
- Fully shielded, insulated and submersible
- Optional features include test point, integral seal, cold shrink jacket seal kit or shield adapter kit

### General

Connector Type	ProbeLok Bi-Metal
Integral Seal	No
Type	200Amp Load Break
With Seal Kit	Yes
With Test Point	No

### Dimensions

Cable Insulation Diameter Maximum	0.730 in
Cable Insulation Diameter Minimum	0.495 in
Weight	3.250 lb

### Electrical Ratings

AC Withstand Voltage (1 min)	34 kV
Amperage Rating	200 A
Basic Impulse Level	95 kV
Corona Extinction (3pC)	11 kV
Current Rating	200 A
DC Withstand Voltage (15 min)	53 kV
Voltage Rating	15 kV

### Conductor Related

Cable Insulation Diameter Range	0.495 - 0.730
Solid or Compacted Conductor	#2 or #3
Stranded or Compressed Conductor	#3 or #4

### Logistics

Standard Package	20
------------------	----

### Product Assets

[Catalogs - Cable Accessories \(C7\)](#)  
[Literature - Loadbreak Elbow Infographic \(GR03087E\)](#)  
[Literature - ProbeLok® connectors](#)  
[SDS - Safety Data Sheet - Versilube G661 Silicone Compound](#)  
[Video - 200A Loadbreak Elbow Fault Closure \(VI03045E\)](#)  
[Video - Grease Best PRactices \(HPS\\_CA\\_UTL\\_VI\\_EN\\_00030\)](#)