

15 kV, Load Break Elbow w/ Test Point, ProbeLok Bimetal Contact, Shield Adapter Kit

By Hubbell Power Systems
Catalog # [215LE32PTS](#)

Load Break Elbow, 200 Amp, 15 kV, with Test Point, Long ProbeLok Bimetal Contact, Shield Adapter Kit, Cable Insulation Diameter range = 0.495 - 0.730 inches, #2 or #3 Solid or Compacted and #3 or #4 Stranded or Compressed



*Representative Image

Features

- Meets or Exceeds IEEE Std. 386 and IEEE Std. 592 requirements
- Interchangeable with other products meeting the same requirements
- Fully shielded, insulated and submersible
- Optional features include test point, integral seal, cold shrink jacket seal kit or shield adapter kit

General

| | |
|----------------|-------------------|
| Connector Type | ProbeLok Bi-Metal |
| Integral Seal | No |
| Type | 200Amp Load Break |
| With Seal Kit | Yes |

Dimensions

| | |
|-----------------------------------|----------|
| Cable Insulation Diameter Maximum | 0.730 in |
| Cable Insulation Diameter Minimum | 0.495 in |
| Weight | 3.250 lb |

Electrical Ratings

| | |
|-------------------------------|-------|
| AC Withstand Voltage (1 min) | 34 kV |
| Amperage Rating | 200 A |
| Basic Impulse Level | 95 kV |
| Corona Extinction (3pC) | 11 kV |
| Current Rating | 200 A |
| DC Withstand Voltage (15 min) | 53 kV |
| Voltage Rating | 15 kV |

Conductor Related

| | |
|----------------------------------|---------------|
| Cable Insulation Diameter Range | 0.495 - 0.730 |
| Solid or Compacted Conductor | #2 or #3 |
| Stranded or Compressed Conductor | #3 or #4 |

Logistics

| | |
|------------------|----|
| Standard Package | 20 |
|------------------|----|

Product Assets

- [Catalogs - Cable Accessories \(C7\)](#)
- [Literature - Loadbreak Elbow Infographic \(GR03087E\)](#)
- [Literature - ProbeLok® connectors](#)
- [SDS - Safety Data Sheet - Versilube G661 Silicone Compound](#)
- [Video - 200A Loadbreak Elbow Fault Closure \(VI03045E\)](#)
- [Video - Grease Best PRactices \(HPS_CA_UTL_VI_EN_00030\)](#)