

15 kV Class Elbow Arrester (12.7 kV MCOV)

By Hubbell Power Systems
Catalog # [215ELA15](#)

Deadfront Elbow Arrester, 15kV 12.7 MCOV

Features

- Meets or Exceeds IEEE Std. 386 and IEEE Std. C62.11. Section 8.1 requirements
- Interchangeable with other products meeting the same requirements
- Fully shielded, insulated and submersible

General

Catalog Number	215ELA15
EU RoHS Indicator	No
Grounding Style	36 in Line Lead
Material	Polymer
Type	Underground Arresters
UPC	096359360490

Dimensions

Dimensions	9.500 in x 8.500 in x 4.000 in
Height	4 in
Length	9.5 in
Maximum Operating Altitude	6000 ft
Weight	5.2 lb
Width	8.5 in

Electrical Ratings

Duty Cycle	15 kV
MCOV	12.7 kV
Maximum Discharge Voltage	• 45.5 kV @ 1.5 kA • 48.5 kV @ 3 kA



	• 52 kV @ 5 kA • 57.5 kV @ 10 kA • 67.5 kV @ 20 kA • 87.5 kV @ 40 kA
Maximum Switching Surge Protective Level @ 500A kV Class	40 kV 15 kV

Certifications And Compliance

Buy America(n) Qualified	TAA Compliant (All status valid till December 2024)
--------------------------	---

Logistics

Carton Quantity	1
Pallet Quantity	108
Standard Package	1

Product Assets

- [Catalogs - Cable Accessories](#)
- [Catalogs - Underground Arresters](#)
- [Installation Manuals - Elbow Arrester Installation and Operation Instructions](#)
- [Literature - Application Guide: Metal-oxide Surge Arresters for use on AC systems](#)
- [Sales Drawings - 15 kV, 200A Loadbreak Elbow Arrester Specifications - 215ELA15](#)
- [Video - Hubbell Power Systems Elbow Arrester](#)
- [Video - Hubbell Power Systems Metal Oxide Varistor](#)
- [Video - Grease Best PRactices](#)