

15 kV Class Elbow Arrester (15.3 kV MCOV)

By Hubbell Power Systems
Catalog # [215ELA18](#)

Deadfront Elbow Arrester, 15kV 15.3 MCOV

Features

- Meets or Exceeds IEEE Std. 386 and IEEE Std. C62.11. Section 8.1 requirements
- Interchangeable with other products meeting the same requirements
- Fully shielded, insulated and submersible

General

Catalog Number	215ELA18
EU RoHS Indicator	No
Grounding Style	36 in Line Lead
Material	Polymer
Type	Underground Arresters
UPC	096359392941

Dimensions

Dimensions	9.500 in x 8.500 in x 4.000 in
Height	4 in
Length	9.5 in
Maximum Operating Altitude	6000 ft
Weight	5.2 lb
Width	8.5 in

Electrical Ratings

Duty Cycle	18 kV
MCOV	15.3 kV
Maximum Discharge Voltage	• 52 kV @ 1.5 kA



- 56 kV @ 3 kA
- 60 kV @ 5 kA
- 66 kV @ 10 kA
- 78 kV @ 20 kA
- 101 kV @ 40 kA

Maximum Switching Surge Protective Level @ 500A kV Class	46 kV 15 kV
--	----------------

Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
--------------------------	----------------------

Logistics

Pallet Quantity	108
Standard Package	1

Product Assets

- [Catalogs - Cable Accessories](#)
- [Catalogs - Underground Arresters](#)
- [Installation Manuals - Elbow Arrester Installation and Operation Instructions](#)
- [Literature - Application Guide: Metal-oxide Surge Arresters for use on AC systems](#)
- [Sales Drawings - Elbow Arrester 15.3 KV MCOV](#)
- [Specifications - 215ELA18](#)
- [Video - Hubbell Power Systems Elbow Arrester](#)
- [Video - Hubbell Power Systems Metal Oxide Varistor](#)
- [Video - Grease Best PRactices](#)