

**15 kV, Load Break Elbow w/ Bimetal Contact, Seal Kit**

By Hubbell Power Systems  
Catalog # [215LE34J](#)

Load Break Elbow, 200 Amp, 15 kV, Long Bimetal Contact, Cable Insulation Diameter range = 0.495 - 0.730 inches, 1/0 Solid or Compacted and #1 Stranded or Compressed

**Features**

- Meets or Exceeds IEEE Std. 386 and IEEE Std. 592 requirements
- Interchangeable with other products meeting the same requirements
- Fully shielded, insulated and submersible
- Optional features include test point, integral seal, cold shrink jacket seal kit or shield adapter kit

**General**

|                       |                   |
|-----------------------|-------------------|
| Catalog Number        | 215LE34J          |
| Connector Type        | Bi-Metal          |
| Integral Seal         | No                |
| PROBELOK ? Connectors | No                |
| Type                  | 200Amp Load Break |
| With Seal Kit         | Yes               |
| With Test Point       | No                |

**Dimensions**

|                                   |          |
|-----------------------------------|----------|
| Cable Insulation Diameter Maximum | 0.73 in  |
| Cable Insulation Diameter Minimum | 0.495 in |
| Weight                            | 3.25 lb  |

**Electrical Ratings**

|                              |       |
|------------------------------|-------|
| AC Withstand Voltage (1 min) | 34 kV |
| Basic Impulse Level          | 95 kV |
| Corona Extinction (3pC)      | 11 kV |



\*Representative Image

|                |       |
|----------------|-------|
| Current Rating | 200 A |
| kV Class       | 15 kV |

**Conductor Related**

|                                  |               |
|----------------------------------|---------------|
| Cable Insulation Diameter Range  | 0.495 - 0.730 |
| Solid or Compacted Conductor     | 1/0           |
| Stranded or Compressed Conductor | #1            |

**Logistics**

|                  |    |
|------------------|----|
| Standard Package | 20 |
|------------------|----|

**Product Assets**

- [Catalogs - Cable Accessories](#)
- [Installation Manuals - Recommended Crimp Tools and Dies for 200A Elbow Bi-Metal Connectors](#)
- [Installation Manuals - 200A, 15kV & 25kV Class Elbows](#)
- [Literature - Loadbreak Elbow Infographic](#)
- [SDS - VERSILUBE G661 SILICONE COMPOUND](#)
- [Specifications - 215LE34J](#)
- [Test Documents - ANSI/IEEE Design Test Report - 15kV 200A Loadbreak Separable Connectors](#)
- [Video - Hubbell Power Systems In Depth: Proper Torque for Underground Cable Accessories](#)
- [Video - Hubbell Power Systems 15kv & 25kv 200A Redesigned Elbow](#)
- [Video - Hubbell Power Systems 200A Loadbreak Elbow Installation](#)