

**15 kV, Load Break Elbow w/ Bimetal Contact, Seal Kit**

By Hubbell Power Systems  
Catalog # [215LE43J](#)

Load Break Elbow, 200 Amp, 15 kV, Long Bimetal Contact, Cable Insulation Diameter range = 0.635 - 0.905 inches, #1 Solid or Compacted and #2 Stranded or Compressed

**Features**

- Meets or Exceeds IEEE Std. 386 and IEEE Std. 592 requirements
- Interchangeable with other products meeting the same requirements
- Fully shielded, insulated and submersible
- Optional features include test point, integral seal, cold shrink jacket seal kit or shield adapter kit

**General**

Catalog Number	215LE43J
Connector Type	Bi-Metal
Integral Seal	No
PROBELOK ? Connectors	No
Type	200Amp Load Break
UPC	096359571971
With Seal Kit	Yes
With Test Point	No

**Dimensions**

Cable Insulation Diameter Maximum	0.905 in
Cable Insulation Diameter Minimum	0.635 in
Weight	3.25 lb

**Electrical Ratings**

AC Withstand Voltage (1 min)	34 kV
Basic Impulse Level	95 kV
Corona Extinction (3pC)	11 kV
Current Rating	200 A
kV Class	15 kV



\*Representative Image

**Conductor Related**

Cable Insulation Diameter Range	0.635 - 0.905
Solid or Compacted Conductor	#1
Stranded or Compressed Conductor	#2

**Certifications And Compliance**

Buy America(n) Qualified	TAA Compliant (All status valid till December 2024)
--------------------------	---

**Logistics**

Pallet Quantity	120
Standard Package	20

**Product Assets**

[Catalogs - Cable Accessories](#)  
[Installation Manuals - Recommended Crimp Tools and Dies for 200A Elbow Bi-Metal Connectors](#)  
[Installation Manuals - 200A, 15kV & 25kV Class Elbows](#)  
[Literature - Loadbreak Elbow Infographic](#)  
[SDS - VERSILUBE G661 SILICONE COMPOUND](#)  
[Specifications - 215LE43J](#)  
[Test Documents - ANSI/IEEE Design Test Report - 15kV 200A Loadbreak Separable Connectors](#)  
[Video - Hubbell Power Systems In Depth: Proper Torque for Underground Cable Accessories](#)  
[Video - Hubbell Power Systems 15kv & 25kv 200A Redesigned Elbow](#)  
[Video - Hubbell Power Systems 200A Loadbreak Elbow Installation](#)