

# 15 kV, Load Break Elbow w/ Bimetal Contact

By Hubbell Power Systems  
Catalog # [215LE53](#)

Load Break Elbow, 200 Amp, 15 kV, Long Bimetal Contact, Cable Insulation Diameter range = 0.760 - 1.135 inches, #1 Solid or Compacted and #2 Stranded or Compressed

## Features

- Meets or Exceeds IEEE Std. 386 and IEEE Std. 592 requirements
- Interchangeable with other products meeting the same requirements
- Fully shielded, insulated and submersible
- Optional features include test point, integral seal, cold shrink jacket seal kit or shield adapter kit

## General

|                       |                   |
|-----------------------|-------------------|
| Catalog Number        | 215LE53           |
| Connector Type        | Bi-Metal          |
| Integral Seal         | No                |
| PROBELOK ? Connectors | No                |
| Type                  | 200Amp Load Break |
| UPC                   | 096359713333      |
| With Seal Kit         | No                |
| With Test Point       | No                |

## Dimensions

|                                   |          |
|-----------------------------------|----------|
| Cable Insulation Diameter Maximum | 1.135 in |
| Cable Insulation Diameter Minimum | 0.76 in  |
| Weight                            | 2.75 lb  |

## Electrical Ratings

|                              |       |
|------------------------------|-------|
| AC Withstand Voltage (1 min) | 34 kV |
| Basic Impulse Level          | 95 kV |
| Corona Extinction (3pC)      | 11 kV |



|                |       |
|----------------|-------|
| Current Rating | 200 A |
| kV Class       | 15 kV |

## Conductor Related

|                                  |               |
|----------------------------------|---------------|
| Cable Insulation Diameter Range  | 0.760 - 1.135 |
| Solid or Compacted Conductor     | #1            |
| Stranded or Compressed Conductor | #2            |

## Logistics

|                  |     |
|------------------|-----|
| Pallet Quantity  | 240 |
| Standard Package | 20  |

## Product Assets

- [Catalogs - Cable Accessories](#)
- [Installation Manuals - Recommended Crimp Tools and Dies for 200A Elbow Bi-Metal Connectors](#)
- [Installation Manuals - 200A, 15kV & 25kV Class Elbows](#)
- [Literature - Loadbreak Elbow Infographic](#)
- [SDS - VERSILUBE G661 SILICONE COMPOUND](#)
- [Specifications - 215LE53](#)
- [Test Documents - ANSI/IEEE Design Test Report - 15kV 200A Loadbreak Separable Connectors](#)
- [Video - Hubbell Power Systems In Depth: Proper Torque for Underground Cable Accessories](#)
- [Video - Hubbell Power Systems 15kv & 25kv 200A Redesigned Elbow](#)
- [Video - Hubbell Power Systems 200A Loadbreak Elbow Installation](#)