

15 kV, Load Break Elbow w/ Bimetal Contact, Seal Kit

By Hubbell Power Systems
Catalog # [215LE54J](#)

Load Break Elbow, 200 Amp, 15 kV, Long Bimetal Contact, Cable Insulation Diameter range = 0.760 - 1.135 inches, 1/0 Solid or Compacted and #1 Stranded or Compressed

Features

- Meets or Exceeds IEEE Std. 386 and IEEE Std. 592 requirements
- Interchangeable with other products meeting the same requirements
- Fully shielded, insulated and submersible
- Optional features include test point, integral seal, cold shrink jacket seal kit or shield adapter kit

General

Catalog Number	215LE54J
Connector Type	Bi-Metal
Integral Seal	No
PROBELOK ? Connectors	No
Type	200Amp Load Break
With Seal Kit	Yes
With Test Point	No

Dimensions

Cable Insulation Diameter Maximum	1.135 in
Cable Insulation Diameter Minimum	0.76 in
Weight	3.25 lb

Electrical Ratings

AC Withstand Voltage (1 min)	34 kV
Basic Impulse Level	95 kV
Corona Extinction (3pC)	11 kV



*Representative Image

Current Rating	200 A
kV Class	15 kV

Conductor Related

Cable Insulation Diameter Range	0.760 - 1.135
Solid or Compacted Conductor	1/0
Stranded or Compressed Conductor	#1

Logistics

Pallet Quantity	120
Standard Package	20

Product Assets

- [Catalogs - Cable Accessories](#)
- [Installation Manuals - Recommended Crimp Tools and Dies for 200A Elbow Bi-Metal Connectors](#)
- [Installation Manuals - 200A, 15kV & 25kV Class Elbows](#)
- [Literature - Loadbreak Elbow Infographic](#)
- [SDS - VERSILUBE G661 SILICONE COMPOUND](#)
- [Specifications - 215LE54J](#)
- [Test Documents - ANSI/IEEE Design Test Report - 15kV 200A Loadbreak Separable Connectors](#)
- [Video - Hubbell Power Systems In Depth: Proper Torque for Underground Cable Accessories](#)
- [Video - Hubbell Power Systems 15kv & 25kv 200A Redesigned Elbow](#)
- [Video - Hubbell Power Systems 200A Loadbreak Elbow Installation](#)