

25/28kV Fused Elbow, with cable insulation dia of 0.920 - 1.185 in, Cooper Fuse Connector

By Hubbell Power Systems
Catalog # [228FECC8](#)

Fused Elbow, 25/28 kV, with Test Point, Cable Insulation Diameter range = 0.920 - 1.185 inches, 250 Compact and 4/0 Stranded or Compressed, Accepts Cooper Current Limiting Fuses



*Representative Image

Features

- Meets or Exceeds IEEE Std. 386 and IEEE Std. 592 requirements
- Interchangeable with other products meeting the same requirements
- Fully shielded, insulated and submersible
- Optional features include test point, integral seal, cold shrink jacket seal kit or shield adapter kit

General

Connector Type	Cooper Fuse Connector
Integral Seal	No
PROBELOK [®] Connectors	No
Type	200A Loadbreak
With Seal Kit	No
With Test Point	Yes

Dimensions

Cable Insulation Diameter Maximum	1.185 in
Cable Insulation Diameter Minimum	0.920 in
Weight	7.5 lb

Electrical Ratings

AC Withstand Voltage (1 min)	45 kV
Basic Impulse Level	125 kV
Corona Extinction (3pC)	21.5 kV
Current Rating	200 A
kV Class	25/28 kV

Conductor Related

Cable Insulation Diameter Range	0.920 - 1.185
Solid or Compacted Conductor	250
Stranded or Compressed Conductor	4/0

Logistics

Standard Package	1
------------------	---

Product Assets

[Catalogs - Cable Accessories \(C7\)](#)
[Installation Manuals - IS200FE_-_Fused_Elbow_Installation_Instructions](#)
[Sales Drawings - 228FE Sales Drawing](#)
[Test Documents - 28kV Fused Elbow Test Report](#)
[Video - Grease Best Practices \(HPS_CA_UTL_VI_EN_00030\)](#)