

25/28 kV Load Break Elbow, 200 Amp, with Test Point, Size 4

By Hubbell Power Systems
Catalog # 228LE40T

Load Break Elbow, 200 Amp, 25/28 kV, with Test Point.



*Representative Image

Features

- Meets or Exceeds IEEE Std. 386 and IEEE Std. 592 requirements
- Interchangeable with other products meeting the same requirements
- Fully shielded, insulated and submersible
- Optional features include test point, integral seal, cold shrink jacket seal kit or shield adapter kit

General

Integral Seal	No
PROBELOK® Connectors	No
Type	200Amp Load Break
UPC	096359639060
With Seal Kit	No
With Test Point	Yes

Dimensions

Cable Insulation Diameter Maximum	1.140 in
Cable Insulation Diameter Minimum	0.800 in
Weight	3.000 lb

Electrical Ratings

AC Withstand Voltage (1 min)	40 kV
Basic Impulse Level	125 kV
Corona Extinction (3pC)	19 kV
Current Rating	200 A
kV Class	25/28 kV

Conductor Related

Cable Insulation Diameter Range	0.800 - 1.140
---------------------------------	---------------

Logistics

Pallet Quantity	72
Standard Package	20

Product Assets

[Catalogs - Cable Accessories \(C7\)](#)
[Literature - Loadbreak Elbow Infographic \(GR03087E\)](#)
[SDS - VERSILUBE G661 SILICONE COMPOUND](#)
[Test Documents - Cable Accessories Test Report - 28kV Class 200A Loadbreak Separable Connectors \(EU1552\)](#)
[Video - 200A Loadbreak Elbow Fault Closure \(VI03045E\)](#)
[Video - Grease Best PRactices \(HPS_CA_UTL_VI_EN_00030\)](#)