

15 kV, Load Break Elbow w/ Integral Seal, Test Point, Bimetal Contact

By Hubbell Power Systems
Catalog # [215LEJ45T](#)

Load Break Elbow with Integral Seal, 200 Amp, 15 kV, with Test Point, Long Bimetal Contact, Cable Insulation Diameter range = 0.635 - 0.905 inches, 2/0 Solid or Compacted and 1/0 Stranded or Compressed

Features

- Meets or Exceeds IEEE Std. 386 and IEEE Std. 592 requirements
- Interchangeable with other products meeting the same requirements
- Fully shielded, insulated and submersible
- Optional features include test point, integral seal, cold shrink jacket seal kit or shield adapter kit

General

| | |
|-----------------------|-------------------|
| Catalog Number | 215LEJ45T |
| Connector Type | Bi-Metal |
| EU RoHS Indicator | No |
| Integral Seal | Yes |
| PROBELOK ? Connectors | No |
| Type | 200Amp Load Break |
| UPC | 096359496311 |
| With Seal Kit | No |
| With Test Point | Yes |

Dimensions

| | |
|-----------------------------------|------------------------------|
| Cable Insulation Diameter Maximum | 0.905 in |
| Cable Insulation Diameter Minimum | 0.635 in |
| Dimensions | 13.00 in x 9.00 in x 4.00 in |
| Height | 4 in |
| Length | 13 in |
| Weight | 2.9 lb |
| Width | 9 in |

Electrical Ratings

| | |
|------------------------------|-------|
| AC Withstand Voltage (1 min) | 34 kV |
| Basic Impulse Level | 95 kV |



*Representative Image

| | |
|-------------------------|-------|
| Corona Extinction (3pC) | 11 kV |
| Current Rating | 200 A |
| kV Class | 15 kV |

Conductor Related

| | |
|----------------------------------|---------------|
| Cable Insulation Diameter Range | 0.635 - 0.905 |
| Solid or Compacted Conductor | 2/0 |
| Stranded or Compressed Conductor | 1/0 |

Certifications And Compliance

| | |
|--------------------------|---|
| Buy America(n) Qualified | TAA Compliant (All status valid till December 2024) |
|--------------------------|---|

Logistics

| | |
|------------------|-----|
| Pallet Quantity | 240 |
| Standard Package | 20 |

Product Assets

[Catalogs - Cable Accessories](#)
[Installation Manuals - Recommended Crimp Tools and Dies for 200A Elbow Bi-Metal Connectors](#)
[Literature - Loadbreak Elbow Infographic](#)
[Sales Drawings - Elbow, 200A 15 kV](#)
[SDS - VERSILUBE G661 SILICONE COMPOUND](#)
[Specifications - 215LEJ45T](#)
[Test Documents - ANSI/IEEE Design Test Report - 15kV 200A Loadbreak Separable Connectors](#)
[Video - Hubbell Power Systems In Depth: Proper Torque for Underground Cable Accessories](#)
[Video - Hubbell Power Systems 15kv & 25kv 200A Redesigned Elbow](#)
[Video - Hubbell Power Systems 200A Loadbreak Elbow Installation](#)