

## 35 kV, Load Break Elbow w/ Bimetal Contact, Shield Adapter Kit

By Hubbell Power Systems  
Catalog # [236LE54S](#)

Load Break Elbow, 200 Amp, 35 kV, Long Bimetal Contact, Shield Adapter Kit, Cable Insulation Diameter range = 1.020 - 1.310 inches, 1/0 Solid or Compacted and #1 Stranded or Compressed



\*Representative Image

### Features

- Meets or Exceeds IEEE Std. 386 and IEEE Std. 592 requirements
- Interchangeable with other products meeting the same requirements
- Fully shielded, insulated and submersible
- Optional features include test point, integral seal, cold shrink jacket seal kit or shield adapter kit

### General

Connector Type	Bi-Metal
PROBELOK® Connectors	No
Type	200Amp Load Break
With Seal Kit	No
With Test Point	No

### Dimensions

Cable Insulation Diameter Maximum	1.310 in
Cable Insulation Diameter Minimum	1.020 in
Weight	5.500 lb

### Electrical Ratings

AC Withstand Voltage (1 min)	50 kV
Amperage Rating	200 A
Basic Impulse Level	150 kV
Corona Extinction (3pC)	26 kV
Current Rating	200 A
DC Withstand Voltage (15 min)	103 kV
Voltage Rating	35 kV
kV Class	Large Interface 35 kV

### Conductor Related

Cable Insulation Diameter Range	1.020 - 1.310
Solid or Compacted Conductor	1/0
Stranded or Compressed Conductor	#1

### Logistics

Standard Package	20
------------------	----

### Product Assets

[Catalogs - Cable Accessories \(C7\)](#)  
[Literature - Loadbreak Elbow Infographic \(GR03087E\)](#)  
[SDS - Safety Data Sheet - Versilube G661 Silicone Compound](#)  
[Video - 200A Loadbreak Elbow Fault Closure \(VI03045E\)](#)  
[Video - Grease Best Practices \(HPS\\_CA\\_UTL\\_VI\\_EN\\_00030\)](#)