

25 kV Class Elbow Arrester (17 kV MCOV)

By Hubbell Power Systems
Catalog # [225ELA21](#)

Deadfront Elbow Arrester, 25kV 17 MCOV

Features

- Meets or Exceeds IEEE Std. 386 and IEEE Std. C62.11. Section 8.1 requirements
- Interchangeable with other products meeting the same requirements
- Fully shielded, insulated and submersible

General

Catalog Number	225ELA21
EU RoHS Indicator	No
Grounding Style	36 in Line Lead
Material	Polymer
Type	Underground Arresters
UPC	096359266655

Dimensions

Dimensions	13.00 in x 7.50 in x 4.00 in
Height	4 in
Length	13 in
Maximum Operating Altitude	6000 ft
Weight	5.2 lb
Width	7.5 in

Electrical Ratings

Duty Cycle	21 kV
MCOV	17 kV
Maximum Discharge Voltage	• 55 kV @ 1.5 kA • 60 kV @ 3 kA



	• 64 kV @ 5 kA • 73 kV @ 10 kA • 84 kV @ 20 kA • 107 kV @ 40 kA
Maximum Switching Surge Protective Level @ 500A kV Class	49 kV 25 kV

Certifications And Compliance

Buy America(n) Qualified	TAA Compliant (All status valid till December 2024)
--------------------------	---

Logistics

Pallet Quantity	108
Standard Package	1

Product Assets

- [Catalogs - Cable Accessories](#)
- [Catalogs - Underground Arresters](#)
- [Installation Manuals - Elbow Arrester Installation and Operation Instructions](#)
- [Literature - Application Guide: Metal-oxide Surge Arresters for use on AC systems](#)
- [Sales Drawings - 225ELA21_SalesDrawing](#)
- [Specifications - 225ELA21](#)
- [Video - Hubbell Power Systems Elbow Arrester](#)
- [Video - Hubbell Power Systems Metal Oxide Varistor](#)
- [Video - Grease Best PRactices](#)