

Cable Adapter

By Hubbell Power Systems
Catalog # [635CAV](#)

35kV 600/900A Cable Adapter, Cable Insulation Diameter
Range = 2.025 - 2.145 Inches



Features

- Meets or Exceeds IEEE Std. 386 and IEEE Std. 592 requirements
- Interchangeable with other products meeting the same requirements
- Stepped design

General

Type Adapters
UPC 096359764311

Dimensions

Cable Insulation Diameter
Maximum 2.145 in
Cable Insulation Diameter
Minimum 2.025 in

Electrical Ratings

AC Withstand Voltage (1 min) 50 kV
Basic Impulse Level 200 kV
Corona Extinction (3pC) 26 kV
kV Class 35 kV

Conductor Related

Cable Insulation Diameter
Range 2.025 - 2.145

Logistics

Pallet Quantity 1536
Standard Package 12

Product Assets

[Catalogs - Cable Accessories \(C7\)](#)
[Installation Manuals - IS635BT Installation & Operating Instructions \(TD03052E_IS635BT\)](#)
[Sales Drawings - 35kV Cable Adapters \(635CA\)](#)
[SDS - Safety Data Sheet - Versilube G661 Silicone Compound](#)
[Test Documents - 35kV Class 600 Deadbreak Connector Test Report](#)
[Video - Grease Best Practices \(HPS_CA_UTL_VI_EN_00030\)](#)