

**25/28kV Fused Elbow, with cable insulation dia of 0.720 - 0.985 in, Cooper Fuse Connector**

By Hubbell Power Systems  
Catalog # [228FECB3](#)



Fused Elbow, 25/28 kV, with Test Point, Cable Insulation Diameter range = 0.720 - 0.985 inches, #1 Solid or Compact and #2 Stranded or Compressed, Accepts Cooper Current Limiting Fuses

**Features**

- Meets or Exceeds IEEE Std. 386 and IEEE Std. 592 requirements
- Interchangeable with other products meeting the same requirements
- Fully shielded, insulated and submersible
- Optional features include test point, integral seal, cold shrink jacket seal kit or shield adapter kit

**General**

Catalog Number	228FECB3
Connector Type	Cooper Fuse Connector
Integral Seal	No
PROBELOK ? Connectors	No
Type	200A Loadbreak
With Seal Kit	No
With Test Point	Yes

**Dimensions**

Cable Insulation Diameter Maximum	0.985 in
Cable Insulation Diameter Minimum	0.72 in
Weight	7.5 lb

**Electrical Ratings**

AC Withstand Voltage (1 min)	45 kV
Basic Impulse Level	125 kV
Corona Extinction (3pC)	21.5 kV
Current Rating	200 A
kV Class	25/28 kV

**Conductor Related**

Cable Insulation Diameter Range	0.720 - 0.985
Solid or Compacted Conductor	#1
Stranded or Compressed Conductor	#2

**Logistics**

Standard Package	1
------------------	---

**Product Assets**

[Catalogs - Cable Accessories](#)  
[Installation Manuals - IS200FE\\_ - \\_Fused\\_Elbow\\_Installation\\_Instructions](#)  
[Sales Drawings - 228FE Sales Drawing](#)  
[Specifications - 228FECB3](#)  
[Test Documents - 28kV Fused Elbow Test Report](#)  
[Video - Grease Best PRactices](#)