

25/28 kV Load Break Elbow, 200
Amp, with Test Point, Size 3

By Hubbell Power Systems
Catalog # [228LE30T](#)

Load Break Elbow, 200 Amp, 25/28 kV, with Test Point.



*Representative Image

Features

- Meets or Exceeds IEEE Std. 386 and IEEE Std. 592 requirements
- Interchangeable with other products meeting the same requirements
- Fully shielded, insulated and submersible
- Optional features include test point, integral seal, cold shrink jacket seal kit or shield adapter kit

General

Catalog Number	228LE30T
Integral Seal	No
PROBELOK ? Connectors	No
Type	200Amp Load Break
UPC	096359829881
With Seal Kit	No
With Test Point	Yes

Dimensions

Cable Insulation Diameter Maximum	0.88 in
Cable Insulation Diameter Minimum	0.61 in
Weight	3 lb

Electrical Ratings

AC Withstand Voltage (1 min)	40 kV
Basic Impulse Level	125 kV
Corona Extinction (3pC)	19 kV
Current Rating	200 A
kV Class	25/28 kV

Conductor Related

Cable Insulation Diameter Range	0.610 - 0.880
------------------------------------	---------------

Logistics

Pallet Quantity	240
Standard Package	20

Product Assets

- [Catalogs - Cable Accessories](#)
- [Literature - Loadbreak Elbow Infographic](#)
- [SDS - VERSILUBE G661 SILICONE COMPOUND](#)
- [Specifications - 228LE30T](#)
- [Test Documents - Cable Accessories Test Report - 28kV Class 200A Loadbreak Separable Connectors](#)
- [Video - Hubbell Power Systems In Depth: Proper Torque for Underground Cable Accessories](#)
- [Video - Hubbell Power Systems 15kv & 25kv 200A Redesigned Elbow](#)
- [Video - Hubbell Power Systems 200A Loadbreak Elbow Installation](#)