

25/28 kV, Load Break Elbow w/ ProbeLok Bimetal Contact

By Hubbell Power Systems
Catalog # [228LE44P](#)



Load Break Elbow, 200 Amp, 25/28 kV, Long ProbeLok Bimetal Contact, Cable Insulation Diameter range = 0.800 - 1.140 inches, 1/0 Solid or Compacted and #1 Stranded or Compressed

Features

- Meets or Exceeds IEEE Std. 386 and IEEE Std. 592 requirements
- Interchangeable with other products meeting the same requirements
- Fully shielded, insulated and submersible
- Optional features include test point, integral seal, cold shrink jacket seal kit or shield adapter kit

General

Catalog Number	228LE44P
Connector Type	ProbeLok Bi-Metal
Integral Seal	No
Type	200Amp Load Break
With Seal Kit	No
With Test Point	No

Dimensions

Cable Insulation Diameter Maximum	1.14 in
Cable Insulation Diameter Minimum	0.8 in
Weight	3 lb

Electrical Ratings

AC Withstand Voltage (1 min)	45 kV
Basic Impulse Level	125 kV
Corona Extinction (3pC)	21 kV
Current Rating	200 A

kV Class	25/28 kV
----------	----------

Conductor Related

Cable Insulation Diameter Range	0.800 - 1.140
Solid or Compacted Conductor	1/0
Stranded or Compressed Conductor	#1

Logistics

Standard Package	20
------------------	----

Product Assets

[Catalogs - Cable Accessories](#)
[Installation Manuals - Recommended Crimp Tools and Dies for 200A Elbow Bi-Metal Connectors](#)
[Installation Manuals - 200A, 15kV & 25kV Class Elbows](#)
[Literature - ProbeLok® connectors](#)
[Literature - Loadbreak Elbow Infographic](#)
[SDS - VERSILUBE G661 SILICONE COMPOUND](#)
[Specifications - 228LE44P](#)
[Test Documents - ProbeLock](#)
[Test Documents - Cable Accessories Test Report - 28kV Class 200A Loadbreak Separable Connectors](#)
[Video - Hubbell Power Systems In Depth: Proper Torque for Underground Cable Accessories](#)
[Video - Hubbell Power Systems 15kv & 25kv 200A Redesigned Elbow](#)
[Video - Hubbell Power Systems 200A Loadbreak Elbow Installation](#)