

**25/28 kV, Load Break Elbow w/  
Test Point, Bimetal Contact, Seal Kit**

By Hubbell Power Systems  
Catalog # [228LE44TJ](#)

Load Break Elbow, 200 Amp, 25/28 kV, with Test Point, Long  
Bimetal Contact, Cable Insulation Diameter range = 0.800 - 1.140  
inches, 1/0 Solid or Compacted and #1 Stranded or Compressed

**Features**

- Meets or Exceeds IEEE Std. 386 and IEEE Std. 592 requirements
- Interchangeable with other products meeting the same requirements
- Fully shielded, insulated and submersible
- Optional features include test point, integral seal, cold shrink jacket seal kit or shield adapter kit

**General**

Catalog Number	228LE44TJ
Connector Type	Bi-Metal
Integral Seal	No
PROBELOK ? Connectors	No
Type	200Amp Load Break
UPC	096359836094
With Seal Kit	Yes
With Test Point	Yes

**Dimensions**

Cable Insulation Diameter Maximum	1.14 in
Cable Insulation Diameter Minimum	0.8 in
Weight	3.5 lb

**Electrical Ratings**

AC Withstand Voltage (1 min)	45 kV
Basic Impulse Level	125 kV
Corona Extinction (3pC)	21 kV



\*Representative Image

Current Rating	200 A
kV Class	25/28 kV

**Conductor Related**

Cable Insulation Diameter Range	0.800 - 1.140
Solid or Compacted Conductor	1/0
Stranded or Compressed Conductor	#1

**Logistics**

Pallet Quantity	120
Standard Package	20

**Product Assets**

[Catalogs - Cable Accessories](#)  
[Installation Manuals - Recommended Crimp Tools and Dies for 200A Elbow Bi-Metal Connectors](#)  
[Installation Manuals - 200A, 15kV & 25kV Class Elbows](#)  
[Literature - Loadbreak Elbow Infographic](#)  
[SDS - VERSILUBE G661 SILICONE COMPOUND](#)  
[Specifications - 228LE44TJ](#)  
[Test Documents - Cable Accessories Test Report - 28kV Class 200A Loadbreak Separable Connectors](#)  
[Video - Hubbell Power Systems In Depth: Proper Torque for Underground Cable Accessories](#)  
[Video - Hubbell Power Systems 15kv & 25kv 200A Redesigned Elbow](#)  
[Video - Hubbell Power Systems 200A Loadbreak Elbow Installation](#)