



## 25/28 kV, Load Break Elbow w/ Integral Seal, Probelok Bimetal Contact

By Hubbell  
Catalog # 228LEJ45P

Load Break Elbow with Integral Seal, 200 Amp, 25/28 kV, Long ProbeLok Bimetal Contact, Cable Insulation Diameter range = 0.800 - 1.140 inches, 2/0 Solid or Compacted and 1/0 Stranded or Compressed



\*Representative Image

### Features

- Meets or Exceeds IEEE Std. 386 and IEEE Std. 592 requirements
- Interchangeable with other products meeting the same requirements
- Fully shielded, insulated and submersible
- Optional features include test point, integral seal, cold shrink jacket seal kit or shield adapter kit

### General

Catalog Number	228LEJ45P
Connector Type	ProbeLok Bi-Metal
Integral Seal	Yes
Type	200Amp Load Break
With Seal Kit	No
With Test Point	No

### Dimensions

Cable Insulation Diameter Maximum	1.14 in
Cable Insulation Diameter Minimum	0.8 in
Weight	3 lb

### Electrical Ratings

AC Withstand Voltage (1 min)	45 kV
Basic Impulse Level	125 kV
Corona Extinction (3pC)	21 kV
Current Rating	200 A
kV Class	25/28 kV

### Conductor Related

Cable Insulation Diameter Range	0.800 - 1.140
Solid or Compacted Conductor	2/0
Stranded or Compressed Conductor	1/0

### Logistics

Standard Package	20
------------------	----

### Product Assets

- [Catalogs - Cable Accessories](#)
- [Installation Manuals - Recommended Crimp Tools and Dies for 200A Elbow Bi-Metal Connectors](#)
- [Literature - Loadbreak Elbow Infographic](#)
- [Literature - ProbeLok® connectors](#)
- [SDS - VERSILUBE G661 SILICONE COMPOUND](#)
- [Test Documents - ProbeLock](#)
- [Test Documents - Cable Accessories Test Report - 28kV Class 200A Loadbreak Separable Connectors](#)
- [Video - Grease Best Practices](#)
- [Video - 200A Loadbreak Elbow Fault Closure](#)



A Hubbell brand