



# 25/28 kV, Load Break Elbow w/ Integral Seal, Test Point, Bimetal Contact

By Hubbell  
Catalog # [228LEJ45T](#)

Load Break Elbow with Integral Seal, 200 Amp, 25/28 kV, with Test Point, Long Bimetal Contact, Cable Insulation Diameter range = 0.800 - 1.140 inches, 2/0 Solid or Compacted and 1/0 Stranded or Compressed



\*Representative Image

## Features

- Meets or Exceeds IEEE Std. 386 and IEEE Std. 592 requirements
- Interchangeable with other products meeting the same requirements
- Fully shielded, insulated and submersible
- Optional features include test point, integral seal, cold shrink jacket seal kit or shield adapter kit

## General

Connector Type	Bi-Metal
EU RoHS Indicator	No
Integral Seal	Yes
PROBELOK ? Connectors	No
Type	200Amp Load Break
UPC	096359590880
With Seal Kit	No
With Test Point	Yes

## Dimensions

Cable Insulation Diameter Maximum	1.14 in
Cable Insulation Diameter Minimum	0.8 in
Dimensions	14.00 in x 9.50 in x 4.250 in
Height	4.25 in
Length	14 in
Weight	3 lb
Width	9.5 in

## Electrical Ratings

AC Withstand Voltage (1 min)	45 kV
Basic Impulse Level	125 kV
Corona Extinction (3pC)	21 kV
Current Rating	200 A
kV Class	25/28 kV

## Conductor Related

Cable Insulation Diameter Range	0.800 - 1.140
Solid or Compacted Conductor	2/0
Stranded or Compressed Conductor	1/0

## Logistics

Pallet Quantity	240
Standard Package	20

## Product Assets

- [Catalogs - Cable Accessories](#)
- [Installation Manuals - Recommended Crimp Tools and Dies for 200A Elbow Bi-Metal Connectors](#)
- [Literature - Loadbreak Elbow Infographic](#)
- [Sales Drawings - Elbow, 200A 25/28 kV](#)
- [SDS - VERSILUBE G661 SILICONE COMPOUND](#)
- [Test Documents - Cable Accessories Test Report - 28kV Class 200A Loadbreak Separable Connectors](#)
- [Video - Grease Best PRactices](#)
- [Video - 200A Loadbreak Elbow Fault Closure](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
HubbellBrand-228LEJ45T-SPEC-EN | REV 6/2024