

15 kV Class Elbow Arrester (7.65 kV MCOV)

By Hubbell Power Systems
Catalog # [215ELA09](#)

Deadfront Elbow Arrester, 15kV 7.65 MCOV

Features

- Meets or Exceeds IEEE Std. 386 and IEEE Std. C62.11. Section 8.1 requirements
- Interchangeable with other products meeting the same requirements
- Fully shielded, insulated and submersible

General

Catalog Number	215ELA09
EU RoHS Indicator	No
Grounding Style	36 in Line Lead
Material	Polymer
Type	Underground Arresters
UPC	096359266624

Dimensions

Dimensions	9.500 in x 8.500 in x 4.000 in
Height	4 in
Length	9.5 in
Maximum Operating Altitude	6000 ft
Weight	3.7 lb
Width	8.5 in

Electrical Ratings

Duty Cycle	9 kV
MCOV	7.65 kV
Maximum Discharge Voltage	• 26.8 kV @ 1.5 kA • 28 kV @ 3 kA



	• 30 kV @ 5 kA • 33 kV @ 10 kA • 39 kV @ 20 kA • 50.5 kV @ 40 kA
Maximum Switching Surge Protective Level @ 500A kV Class	23 kV 15 kV

Certifications And Compliance

Buy America(n) Qualified	TAA Compliant (All status valid till December 2024)
--------------------------	---

Logistics

Pallet Quantity	160
Standard Package	1

Product Assets

- [Catalogs - Cable Accessories](#)
- [Catalogs - Underground Arresters](#)
- [Installation Manuals - Elbow Arrester Installation and Operation Instructions](#)
- [Literature - Application Guide: Metal-oxide Surge Arresters for use on AC systems](#)
- [Sales Drawings - 15 kV, 200A Loadbreak Elbow Arrester](#)
- [Specifications - 215ELA09](#)
- [Video - Hubbell Power Systems Elbow Arrester](#)
- [Video - Hubbell Power Systems Metal Oxide Varistor](#)
- [Video - Grease Best PRactices](#)