

**15kV Fused Elbow, 0.610 - 0.823**  
**Cable insulation dia range, Cooper**  
**Fuse Connector**

By Hubbell Power Systems  
Catalog # [215FECA3](#)

Fused Elbow, 15 kV, with Test Point, Cable Insulation Diameter range = 0.610 - 0.823 inches, #1 Solid or Compact and #2 Stranded or Compressed, Accepts Cooper Current Limiting Fuses

**Features**

- Meets or Exceeds IEEE Std. 386 and IEEE Std. 592 requirements
- Interchangeable with other products meeting the same requirements
- Fully shielded, insulated and submersible
- Optional features include test point, integral seal, cold shrink jacket seal kit or shield adapter kit

**General**

Catalog Number	215FECA3
Connector Type	Cooper Fuse Connector
EU RoHS Indicator	No
Integral Seal	No
PROBELOK ? Connectors	No
Type	200A Loadbreak
UPC	096359690535
With Seal Kit	No
With Test Point	Yes

**Dimensions**

Cable Insulation Diameter Maximum	0.823 in
Cable Insulation Diameter Minimum	0.61 in
Weight	7 lb

**Electrical Ratings**



\*Representative Image

AC Withstand Voltage (1 min)	34 kV
Basic Impulse Level	95 kV
Corona Extinction (3pC)	11 kV
Current Rating	200 A
kV Class	15 kV

**Conductor Related**

Cable Insulation Diameter Range	0.610 - 0.823
Solid or Compacted Conductor	#1
Stranded or Compressed Conductor	#2

**Certifications And Compliance**

Buy America(n) Qualified	Contact Manufacturer
--------------------------	----------------------

**Logistics**

Pallet Quantity	240
Standard Package	1

**Product Assets**

[Catalogs - Cable Accessories](#)  
[Installation Manuals - IS200FE\\_-  
\\_Fused\\_Elbow\\_Installation\\_Instructions](#)  
[Sales Drawings - 215FE Sales Drawing](#)  
[Specifications - 215FECA3](#)  
[Test Documents - 15kV Fused Elbow Test Report](#)  
[Video - Grease Best PRactices](#)