

15kV Fused Elbow, 0.720 - 0.985
Cable insulation dia range, Cooper
Fuse Connector

By Hubbell Power Systems
Catalog # [215FECB3](#)

Fused Elbow, 15 kV, with Test Point, Cable Insulation Diameter range = 0.720 - 0.985 inches, #1 Solid or Compact and #2 Stranded or Compressed, Accepts Cooper Current Limiting Fuses

Features

- Meets or Exceeds IEEE Std. 386 and IEEE Std. 592 requirements
- Interchangeable with other products meeting the same requirements
- Fully shielded, insulated and submersible
- Optional features include test point, integral seal, cold shrink jacket seal kit or shield adapter kit

General

Catalog Number	215FECB3
Connector Type	Cooper Fuse Connector
Integral Seal	No
PROBELOK ? Connectors	No
Type	200A Loadbreak
With Seal Kit	No
With Test Point	Yes

Dimensions

Cable Insulation Diameter Maximum	0.985 in
Cable Insulation Diameter Minimum	0.72 in
Weight	7 lb

Electrical Ratings



*Representative Image

AC Withstand Voltage (1 min)	34 kV
Basic Impulse Level	95 kV
Corona Extinction (3pC)	11 kV
Current Rating	200 A
kV Class	15 kV

Conductor Related

Cable Insulation Diameter Range	0.720 - 0.985
Solid or Compacted Conductor	#1
Stranded or Compressed Conductor	#2

Logistics

Pallet Quantity	240
Standard Package	1

Product Assets

[Catalogs - Cable Accessories](#)
[Installation Manuals - IS200FE_-_Fused_Elbow_Installation_Instructions](#)
[Sales Drawings - 215FE Sales Drawing](#)
[Specifications - 215FECB3](#)
[Test Documents - 15kV Fused Elbow Test Report](#)
[Video - Grease Best PRactices](#)