

**15 kV, Load Break Elbow w/  
ProbeLok Bimetal Contact, Shield  
Adapter Kit**

By Hubbell Power Systems  
Catalog # [215LE32PS](#)



Load Break Elbow, 200 Amp, 15 kV, Long ProbeLok Bimetal Contact, Shield Adapter Kit, Cable Insulation Diameter range = 0.495 - 0.730 inches, #2 or #3 Solid or Compacted and #3 or #4 Stranded or Compressed

**Features**

- Meets or Exceeds IEEE Std. 386 and IEEE Std. 592 requirements
- Interchangeable with other products meeting the same requirements
- Fully shielded, insulated and submersible
- Optional features include test point, integral seal, cold shrink jacket seal kit or shield adapter kit

**General**

Catalog Number	215LE32PS
Connector Type	ProbeLok Bi-Metal
Integral Seal	No
Type	200Amp Load Break
With Seal Kit	Yes
With Test Point	No

**Dimensions**

Cable Insulation Diameter Maximum	0.73 in
Cable Insulation Diameter Minimum	0.495 in
Weight	3.25 lb

**Electrical Ratings**

AC Withstand Voltage (1 min)	34 kV
Amperage Rating	200 A

Basic Impulse Level	95 kV
Corona Extinction (3pC)	11 kV
Current Rating	200 A
DC Withstand Voltage (15 min)	53 kV
Voltage Rating	15 kV

**Conductor Related**

Cable Insulation Diameter Range	0.495 - 0.730
Solid or Compacted Conductor	#2 or #3
Stranded or Compressed Conductor	#3 or #4

**Logistics**

Standard Package	20
------------------	----

**Product Assets**

- [Catalogs - Cable Accessories](#)
- [Literature - ProbeLok® connectors](#)
- [Literature - Loadbreak Elbow Infographic](#)
- [SDS - Safety Data Sheet - Versilube G661 Silicone Compound](#)
- [Specifications - 215LE32PS](#)
- [Video - Hubbell Power Systems In Depth: Proper Torque for Underground Cable Accessories](#)
- [Video - Hubbell Power Systems 15kv & 25kv 200A Redesigned Elbow](#)
- [Video - Hubbell Power Systems 200A Loadbreak Elbow Installation](#)