



35 kV Class Large Interface Elbow Arrester (29 kV MCOV)

By Hubbell
Catalog # 236ELA36

ELBOW ARRESTER, 35KV 29 MCOV, Mates with IEEE Std. 386, Interface 9



*Representative Image

Features

- Meets or Exceeds IEEE Std. 386 and IEEE Std. C62.11. Section 8.1 requirements
- Interchangeable with other products meeting the same requirements
- Fully shielded, insulated and submersible

General

Catalog Number	236ELA36
EU RoHS Indicator	No
Grounding Style	36 in Line Lead
Type	Underground Arresters
UPC	096359695363

Dimensions

Dimensions	16.688 in x 9.250 in x 4.50 in
Height	4.5 in
Length	16.688 in
Weight	9.4 lb
Width	9.25 in

Electrical Ratings

Duty Cycle	36 kV
------------	-------

MCOV	29 kV
Maximum Discharge Voltage	<ul style="list-style-type: none"> • 117.4 kV @ 1.5 kA • 100.5 kV @ 3 kA • 107.2 kV @ 5 kA • 120.7 kV @ 10 kA • 139.4 kV @ 20 kA • 174.3 kV @ 40 kA
Maximum Switching Surge Protective Level @ 500A	84.5 kV
kV Class	35 kV

Logistics

Pallet Quantity	64
Standard Package	1

Product Assets

- [Catalogs - Cable Accessories](#)
- [Catalogs - Underground Arresters](#)
- [Literature - Application Guide: Metal-oxide Surge Arresters for use on AC systems](#)
- [Sales Drawings - 35 kV, 200A Large interface Loadbreak Elbow Arrester](#)
- [Specifications - 236ELA36](#)
- [Video - Grease Best PRactices](#)
- [Video - Hubbell Power Systems Metal Oxide Varistor](#)