

**15 kV, Load Break Elbow w/ Test Point, Bimetal Contact**

By Hubbell Power Systems  
Catalog # [215LE35T](#)

Load Break Elbow, 200 Amp, 15 kV, with Test Point, Long Bimetal Contact, Cable Insulation Diameter range = 0.495 - 0.730 inches, 2/0 Solid or Compacted and 1/0 Stranded or Compressed

**Features**

- Meets or Exceeds IEEE Std. 386 and IEEE Std. 592 requirements
- Interchangeable with other products meeting the same requirements
- Fully shielded, insulated and submersible
- Optional features include test point, integral seal, cold shrink jacket seal kit or shield adapter kit

**General**

Catalog Number	215LE35T
Connector Type	Bi-Metal
Integral Seal	No
PROBELOK ? Connectors	No
Type	200Amp Load Break
With Seal Kit	No
With Test Point	Yes

**Dimensions**

Cable Insulation Diameter Maximum	0.73 in
Cable Insulation Diameter Minimum	0.495 in
Weight	2.75 lb

**Electrical Ratings**

AC Withstand Voltage (1 min)	34 kV
Basic Impulse Level	95 kV
Corona Extinction (3pC)	11 kV



\*Representative Image

Current Rating	200 A
kV Class	15 kV

**Conductor Related**

Cable Insulation Diameter Range	0.495 - 0.730
Solid or Compacted Conductor	2/0
Stranded or Compressed Conductor	1/0

**Logistics**

Pallet Quantity	240
Standard Package	20

**Product Assets**

- [Catalogs - Cable Accessories](#)
- [Installation Manuals - Recommended Crimp Tools and Dies for 200A Elbow Bi-Metal Connectors](#)
- [Installation Manuals - 200A, 15kV & 25kV Class Elbows](#)
- [Literature - Loadbreak Elbow Infographic](#)
- [SDS - VERSILUBE G661 SILICONE COMPOUND](#)
- [Specifications - 215LE35T](#)
- [Test Documents - ANSI/IEEE Design Test Report - 15kV 200A Loadbreak Separable Connectors](#)
- [Video - Hubbell Power Systems In Depth: Proper Torque for Underground Cable Accessories](#)
- [Video - Hubbell Power Systems 15kv & 25kv 200A Redesigned Elbow](#)
- [Video - Hubbell Power Systems 200A Loadbreak Elbow Installation](#)