



## Modular Splice Kit w/ Test Point, Two Way

By Hubbell  
Catalog # [625L2T](#)

600 Amp Two-way Modular Splice Kit with Test Point.



### Features

- Meets or Exceeds IEEE Std. 386 and IEEE Std. 592 requirements
- Interchangeable with other products meeting the same requirements
- Fully shielded, insulated and submersible
- Optional features include test point, shear bolt connector, cold shrink jacket seal kit or shield adapter kit

### General

EU RoHS Indicator	No
Type	600 Amp Dead Break
UPC	096359393313
With Test Point	Yes

### Dimensions

Weight	15 lb
--------	-------

### Electrical Ratings

AC Withstand Voltage (1 min)	45 kV
Basic Impulse Level	125 kV
Corona Extinction (3pC)	21 kV
Current Rating	600 A
kV Class	15 kV

### Logistics

Pallet Quantity	25
Standard Package	1

### Product Assets

[Catalogs - Cable Accessories](#)  
[Sales Drawings - Module Splicing Kits 600/900 AMP, 25 KV](#)  
[SDS - VERSILUBE G661 SILICONE COMPOUND](#)  
[Video - Grease Best PRactices](#)



A Hubbell brand