

**HC14193797592 TYPE 720 100 AMP
DC CONTACTOR.**

By Hubbell Industrial Controls (ICD)
Catalog # [HC14193797592](#)



TYPE 720, 100A DC CONTACTOR

Features

- UL recognized/CSA certified. NEMA Size 4 . Main Contact Options: SPNO, SPDT, and Series Field Reversal.
- 5 Million mechanical operations. Front access for serviceability. Silver alloy main contact tips. AC or DC operation. High dielectric and mechanical strength.
- Rugged and reliable, this industrial quality device is used in applications such as gas/oil drilling and solid-state adjustable speed drives, uninterruptible power supplies, fuel cells, crane controls, transit and rail, and mining machinery.
- It is rated at 100 Ampere, continuous at 600 VDC in still air (special voltages available consult factory) and can achieve a maximum interrupting rating of 600 kW.

General

Arc chute polarity	Negative
Auxiliary Contacts	2 NO & 2 NC
Catalog Number	HC14193797592
DC Coil Voltage	250
Enclosure Type	NEMA 4.5

Mounting Method	Insulated mounting sheet(1/32" thick) provided with contactor
Operating Temperature Range Celcius	20
Series	720
Type	Definite Purpose

Dimensions

Weight	1.68 lb
--------	---------

Electrical Ratings

Amperage Rating	100 A
Current / Amperage Rating	100 A
Operating Voltage	600 VDC
Resistance	960
Voltage Rating Description	600 V

Product Assets

[Catalogs - 100D DC Devices Brochure](#)
[Catalogs - 42720 200 Amp DC Contactor Catalog](#)
[Specifications - HC14193797592](#)