

15 kV, Load Break Elbow w/ Bimetal  
Contact

By Hubbell Power Systems  
Catalog # [215LE58](#)

Load Break Elbow, 200 Amp, 15 kV, Long Bimetal Contact, Cable  
Insulation Diameter range = 0.760 - 1.135 inches, 250 Solid or  
Compacted and 4/0 Stranded or Compressed

Features

- Meets or Exceeds IEEE Std. 386 and IEEE Std. 592 requirements
- Interchangeable with other products meeting the same requirements
- Fully shielded, insulated and submersible
- Optional features include test point, integral seal, cold shrink jacket seal kit or shield adapter kit

General

|                       |                   |
|-----------------------|-------------------|
| Catalog Number        | 215LE58           |
| Connector Type        | Bi-Metal          |
| EU RoHS Indicator     | No                |
| Integral Seal         | No                |
| PROBELOK ? Connectors | No                |
| Type                  | 200Amp Load Break |
| UPC                   | 096359500834      |
| With Seal Kit         | No                |
| With Test Point       | No                |

Dimensions

|                                      |                             |
|--------------------------------------|-----------------------------|
| Cable Insulation Diameter<br>Maximum | 1.135 in                    |
| Cable Insulation Diameter<br>Minimum | 0.76 in                     |
| Dimensions                           | 9.00 in x 9.00 in x 4.00 in |
| Height                               | 4 in                        |
| Length                               | 9 in                        |
| Weight                               | 2.75 lb                     |
| Width                                | 9 in                        |

Electrical Ratings

|                              |       |
|------------------------------|-------|
| AC Withstand Voltage (1 min) | 34 kV |
| Basic Impulse Level          | 95 kV |
| Corona Extinction (3pC)      | 11 kV |



|                |       |
|----------------|-------|
| Current Rating | 200 A |
| kV Class       | 15 kV |

Conductor Related

|                                     |               |
|-------------------------------------|---------------|
| Cable Insulation Diameter<br>Range  | 0.760 - 1.135 |
| Solid or Compacted Conductor        | 250           |
| Stranded or Compressed<br>Conductor | 4/0           |

Certifications And Compliance

|                          |                                                        |
|--------------------------|--------------------------------------------------------|
| Buy America(n) Qualified | TAA Compliant (All status valid<br>till December 2024) |
|--------------------------|--------------------------------------------------------|

Logistics

|                  |     |
|------------------|-----|
| Pallet Quantity  | 240 |
| Standard Package | 20  |

Product Assets

[Catalogs - Cable Accessories](#)  
[Installation Manuals - Recommended Crimp Tools and Dies for 200A Elbow Bi-Metal Connectors](#)  
[Installation Manuals - 200A, 15kV & 25kV Class Elbows](#)  
[Literature - Loadbreak Elbow Infographic](#)  
[Sales Drawings - Elbow, 200A 15 kV](#)  
[SDS - VERSILUBE G661 SILICONE COMPOUND](#)  
[Specifications - 215LE58](#)  
[Test Documents - ANSI/IEEE Design Test Report - 15kV 200A Loadbreak Separable Connectors](#)  
[Video - Hubbell Power Systems In Depth: Proper Torque for Underground Cable Accessories](#)  
[Video - Hubbell Power Systems 15kv & 25kv 200A Redesigned Elbow](#)  
[Video - Hubbell Power Systems 200A Loadbreak Elbow Installation](#)