

**15 kV, Load Break Elbow w/ Test Point, ProbeLok Bimetal Contact, Shield Adapter Kit**

By Hubbell Power Systems  
Catalog # [215LE58PTS](#)



Load Break Elbow, 200 Amp, 15 kV, with Test Point, Long ProbeLok Bimetal Contact, Shield Adapter Kit, Cable Insulation Diameter range = 0.760 - 1.135 inches, 250 Solid or Compacted and 4/0 Stranded or Compressed

**Features**

- Meets or Exceeds IEEE Std. 386 and IEEE Std. 592 requirements
- Interchangeable with other products meeting the same requirements
- Fully shielded, insulated and submersible
- Optional features include test point, integral seal, cold shrink jacket seal kit or shield adapter kit

**General**

Catalog Number	215LE58PTS
Connector Type	ProbeLok Bi-Metal
Integral Seal	No
Type	200Amp Load Break
With Seal Kit	Yes

**Dimensions**

Cable Insulation Diameter Maximum	1.135 in
Cable Insulation Diameter Minimum	0.76 in
Weight	3.25 lb

**Electrical Ratings**

AC Withstand Voltage (1 min)	34 kV
Amperage Rating	200 A
Basic Impulse Level	95 kV

Corona Extinction (3pC)	11 kV
Current Rating	200 A
DC Withstand Voltage (15 min)	53 kV
Voltage Rating	15 kV

**Conductor Related**

Cable Insulation Diameter Range	0.760 - 1.135
Solid or Compacted Conductor	250
Stranded or Compressed Conductor	4/0

**Logistics**

Standard Package	20
------------------	----

**Product Assets**

[Catalogs - Cable Accessories](#)  
[Literature - ProbeLok® connectors](#)  
[Literature - Loadbreak Elbow Infographic](#)  
[SDS - Safety Data Sheet - Versilube G661 Silicone Compound](#)  
[Specifications - 215LE58PTS](#)  
[Video - Hubbell Power Systems In Depth: Proper Torque for Underground Cable Accessories](#)  
[Video - Hubbell Power Systems 15kv & 25kv 200A Redesigned Elbow](#)  
[Video - Hubbell Power Systems 200A Loadbreak Elbow Installation](#)