



15 kV, Load Break Elbow w/ Integral Seal, Test Point, Bimetal Contact

By Hubbell
Catalog # [215LEJ58T](#)

Load Break Elbow with Integral Seal, 200 Amp, 15 kV, with Test Point, Long Bimetal Contact, Cable Insulation Diameter range = 0.760 - 1.135 inches, 250 Solid or Compacted and 4/0 Stranded or Compressed



*Representative Image

Features

- Meets or Exceeds IEEE Std. 386 and IEEE Std. 592 requirements
- Interchangeable with other products meeting the same requirements
- Fully shielded, insulated and submersible
- Optional features include test point, integral seal, cold shrink jacket seal kit or shield adapter kit

General

Connector Type	Bi-Metal
EU RoHS Indicator	No
Integral Seal	Yes
PROBELOK ? Connectors	No
Type	200Amp Load Break
UPC	096359512318
With Seal Kit	No
With Test Point	Yes

Dimensions

Cable Insulation Diameter Maximum	1.135 in
Cable Insulation Diameter Minimum	0.76 in
Dimensions	13.00 in x 9.00 in x 4.00 in
Height	4 in
Length	13 in
Weight	2.9 lb
Width	9 in

Electrical Ratings

AC Withstand Voltage (1 min)	34 kV
Basic Impulse Level	95 kV
Corona Extinction (3pC)	11 kV
Current Rating	200 A
kV Class	15 kV

Conductor Related

Cable Insulation Diameter Range	0.760 - 1.135
Solid or Compacted Conductor	250
Stranded or Compressed Conductor	4/0

Logistics

Pallet Quantity	240
Standard Package	20

Product Assets

- [Catalogs - Cable Accessories](#)
- [Installation Manuals - Recommended Crimp Tools and Dies for 200A Elbow Bi-Metal Connectors](#)
- [Literature - Loadbreak Elbow Infographic](#)
- [Sales Drawings - Elbow, 200A 15 kV](#)
- [SDS - VERSILUBE G661 SILICONE COMPOUND](#)
- [Test Documents - ANSI/IEEE Design Test Report - 15kV 200A Loadbreak Separable Connectors](#)
- [Video - Grease Best Practices](#)
- [Video - 200A Loadbreak Elbow Fault Closure](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
HubbellBrand-215LEJ58T-SPEC-EN | REV 6/2024