

HUBBELL
Industrial Controls

HC91913002 MAGNET CONTROLLER 4296 12V CT

By Hubbell Industrial Controls (ICD)
Catalog # [HC91913002](#)



TYPE 4296 LIFTING MAGNET CONTROLLER, MANUAL
DISCHARGE RESISTOR, 13-25 AMPS COLD MAGNET CURRENT,
230 VOLTS DC, 12 VOLTS CONTROL CIRCUIT, NEMA 1A/3R
ENCLOSED

General

Series 4296 Euclid
Type Manual Discharge

Dimensions

Dimensions 16.12 in x 10 in x 24.25 in
Height 24.25 in
Length 16.12 in
Width 10 in

Electrical Ratings

Current / Amperage Rating 13-25 A

Certifications And Compliance

Contactors NEMA Rating 1
Enclosure NEMA Rating 1A/3R
Nema Rating NEMA 3R

Product Assets

[Catalogs - 4296 Lifting Magnet Controller Specification](#)

[Catalogs - 4296 Lifting Magnet Controller Catalog](#)

[Catalogs - 100E Euclid Brochure](#)

[Installation Manuals - ICD_4291Pub180_CATALOG](#)