

## 4208 Thruster Drum Brake

By Hubbell Industrial Controls (ICD)

4208 Thruster Drum Brakes are spring set, electrically released, drum type friction brakes used with AC motors

### Features

- 8" to 30" Industrial duty drum brakes
- Torque range available from 50 – 9000 lb-ft.
- Brake lining friction coefficient  $Q = 0.42$
- Electrohydraulic thruster: IP65 rated enclosure
- Thruster motor: Class F insulation (maximum operating temperature 155°C)



- Operating voltage: 230/460 3Ph, 60 Hz
- Thruster hydraulic fluid operating range (-20°C to +55°C)
- AIST TR-11 mounting dimensions

### Product Assets

[Catalogs - 4208 Thruster Drum Brake](#)

[Catalogs - Bullet 4208 Thruster Drum Brakes](#)

[Specifications - 4208 Thruster Drum Brake](#)

