




## 25/28kV Fused Elbow, with cable insulation dia of 0.720 - 0.985 in, Hi-Tech® Fuse Connector

By Hubbell  
Catalog # 228FEHB5J



**Oh No!**  
IMAGE COMING SOON

Fused Elbow, 25/28 kV, with Test Point and jacket seal kit, Cable Insulation Diameter range = 0.720 - 0.985 inches, 2/0 Solid or Compact and 1/0 Stranded or Compressed, Accepts Hi-Tech® EFX Current Limiting Fuses

### Features

- Meets or Exceeds IEEE Std. 386 and IEEE Std. 592 requirements
- Interchangeable with other products meeting the same requirements
- Fully shielded, insulated and submersible
- Optional features include test point, integral seal, cold shrink jacket seal kit or shield adapter kit

### General

Catalog Number	228FEHB5J
Connector Type	Hi-Tech® Fuse Connector
Integral Seal	No
PROBELOK ? Connectors	No
Type	200A Loadbreak
UPC	096359753186
With Seal Kit	Yes
With Test Point	Yes

### Dimensions

Cable Insulation Diameter Maximum	0.985 in
Cable Insulation Diameter Minimum	0.72 in
Weight	7.5 lb

### Electrical Ratings

AC Withstand Voltage (1 min)	45 kV
Basic Impulse Level	125 kV
Corona Extinction (3pC)	21.5 kV
Current Rating	200 A
kV Class	25/28 kV

### Conductor Related

Cable Insulation Diameter Range	0.720 - 0.985
Solid or Compacted Conductor	2/0
Stranded or Compressed Conductor	1/0

### Logistics

Pallet Quantity	240
Standard Package	1

### Product Assets

- [Catalogs - Cable Accessories](#)
- [Installation Manuals - IS200FE\\_-\\_Fused\\_Elbow\\_Installation\\_Instructions](#)
- [Sales Drawings - 228FE Sales Drawing](#)
- [Specifications - 228FEHB5J](#)
- [Test Documents - 28kV Fused Elbow Test Report](#)
- [Video - Grease Best Practices](#)