

**KILLARK®**

**HKH Series Control Station, Red  
Pilot Light and Two Momentary  
Push Buttons- Din Rail Mount- M20 -  
Stainless Steel 1c**

By Killark

Catalog # [HKHMOD000023](#)

HKH Red Pilot Light and Two Momentary Push Buttons- Din Rail  
Mount- M20 - Stainless Steel 1c



## Features

- Size 1 Control Stations available as 1a, 1b, & 1c as standard catalog number offerings for 1, 2 & 3 device openings and will accept 2-M20 entries in either end.
- Ammeters available in 1b & 1c.
- Size 2 Enclosures available as 2a & 2c for 2, 4 & 6 device entries in cover with ability to accept 2-M25 entries in either end.
- Operating Temperature of -50°C to +60°C.
- Explosion Protected contact blocks 690 VAC N.O. & N.C. capable of 20 Amps for Switching Duty and HP Ratings up to 1HP.
- LED Pilot Light modules for 12-250V AC/ DC for UL applications. 12-254V AC/DC for IEC applications.
- Contacts & Pilot lights can be mounted inside enclosure on Din Rail or in cover to the actuator.
- Accessories available for Lockout/Tag Out functions made in 316 stainless steel.

## General

Action	Momentary
Actuator	Pilot Light & Two Pushbuttons
Ambient Temp. Range	-50 °C to 60 °C
Application	Hazardous and corrosive environments due to the presence of flammable gases or vapors, combustible dusts or ignitable fiber or flyings, Installations at petroleum refineries, chemical and petrochemical plants and other processing or storage facilities where similar hazards exist, Use in conjunction with motor starters or contactors for remote control of motors
Catalog Number	HKHMOD000023
Color	Red & Choice of Red, Green, Black
EU RoHS Indicator	Contact Manufacturer
Horsepower - Maximum	1
Material	Plastic
Mounting Type	Wall
Operating Temperature Range Celcius	-50°C to 60°C
Series	HKH
UPC	783936130446

## Dimensions

Depth	4.25
Hub Size	M20
Weight	1.88 lb

## Electrical Ratings

Amperage Rating	20 A
Frequency Rating	50/60 Hz

## Certifications And Compliance

ATEX File Number	1405X
Hazardous Rating(s)	Class I, Division 2, Groups A, B, C, D Class II, Division 1, Groups E, F, G (Canada Only) Class II, Division 2, Groups E, F, G Class III, Divisions 1 & 2 Zones 1 & 2 Zones 21 & 22
IECEX File Number	15.0054X
Nema Rating	3, 4, 4X, 12, 13
UL File Number	E53360

## Product Assets

[3D Models - KIL\\_HKHM000023](#)  
[Brochures - HKH Brochure](#)  
[Catalogs - Killark Catalog](#)  
[Certifications - HKH Inmetro Certificate of Conformity](#)  
[Certifications - HKH Series Control Stations UKCA Certificate](#)  
[Certifications - HKH Series Actuators, Pilotlights, & Plugs](#)  
[Declaration of Conformity](#)  
[Certifications - HKH Series E-Stop Assemblies Attestation of Conformity](#)  
[Certifications - HKH Series Control Stations Declaration of Conformity](#)  
[Certifications - HKH Series Control Stations UL Certification](#)  
[Customer Notices - Prop 65 Notice](#)  
[Installation Manuals - HKH Series Control Stations Installation Manual K1466](#)  
[Sales Drawings - HKHM000023 Sales Drawing](#)  
[Sales Drawings - HKHM000023 Sales Drawing](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
KILL-HKHMODO00023-SPEC-EN | REV 6/2024