



25/28 kV, Load Break Elbow w/ Test Point, ProbeLok Bimetal Contact, Seal Kit

By Hubbell
Catalog # 228LE47PTJ

Load Break Elbow, 200 Amp, 25/28 kV, with Test Point, Long ProbeLok Bimetal Contact, Cable Insulation Diameter range = 0.800 - 1.140 inches, 4/0 Solid or Compacted and 3/0 Stranded or Compressed



Features

- Meets or Exceeds IEEE Std. 386 and IEEE Std. 592 requirements
- Interchangeable with other products meeting the same requirements
- Fully shielded, insulated and submersible
- Optional features include test point, integral seal, cold shrink jacket seal kit or shield adapter kit

General

Catalog Number	228LE47PTJ
Connector Type	ProbeLok Bi-Metal
Integral Seal	No
Type	200Amp Load Break
With Seal Kit	Yes
With Test Point	Yes

Dimensions

Cable Insulation Diameter Maximum	1.14 in
Cable Insulation Diameter Minimum	0.8 in
Weight	3.5 lb

Electrical Ratings

AC Withstand Voltage (1 min)	45 kV
Basic Impulse Level	125 kV
Corona Extinction (3pC)	21 kV
Current Rating	200 A
kV Class	25/28 kV

Conductor Related

Cable Insulation Diameter Range	0.800 - 1.140
Solid or Compacted Conductor	4/0
Stranded or Compressed Conductor	3/0

Logistics

Standard Package	20
------------------	----

Product Assets

- [Catalogs - Cable Accessories](#)
- [Installation Manuals - 200A, 15kV & 25kV Class Elbows](#)
- [Installation Manuals - Recommended Crimp Tools and Dies for 200A Elbow Bi-Metal Connectors](#)
- [Literature - Loadbreak Elbow Infographic](#)
- [Literature - ProbeLok® connectors](#)
- [SDS - VERSILUBE G661 SILICONE COMPOUND](#)
- [Test Documents - ProbeLock](#)
- [Test Documents - Cable Accessories Test Report - 28kV Class 200A Loadbreak Separable Connectors](#)
- [Video - Grease Best PRactices](#)
- [Video - 200A Loadbreak Elbow Fault Closure](#)



A Hubbell brand