



VM4LC6IE230 - VM4LC 6000

Lumen Range Standard with 2000

Lumen Battery Backup 120-277VAC 50/60 Hz

By Killark
Catalog # [VM4LC6IE230](#)



VM4LC 6000 Lumen Range Standard with 2000 Lumen
Battery Backup 120-277VAC 50/60 Hz

Features

- Supplemental 20KA/10KV Surge Protection is standard for 120-277 VAC models & 10KA/10KV Surge Protection is standard for 347-480 VAC models
- Traditional Industrial Appearance, Suitability, and Photometric Performance
- Wide variety of optics including globes, globes with reflectors, all-glass refractors, spin-top refractors and flat lens
- Swing-Barrel Nut patented tank mounting system
- Optional Mounting arrangements including Pendant, Wall, Ceiling, Stanchion and others
- VM4L LED Housings can be retrofitted to existing VM splice boxes to upgrade from HID sources
- Crisp White Light for Excellent Color Rendering – Chromaticity 5000 K (CCT range) approx. 70 CRI
- Energy Savings – less than 130 Watts of Power
- Long Life – 50,000 – 55,000 maintenance free hours to 70% initial lumens
- Instant On – Including after power interruption
- World Voltage 120 – 277VAC 50/60Hz
- Solder-LESS LED Board Connections – Vibration Resistant
- LM79-08 Certified “Absolute” Photometry, including Chromaticity Color for Solid State Lighting

General

Color Temperature	5000 K
Finish Type	Powder Epoxy Paint
Light Source	LED
Lumen Range	5,001-10,000 lm
Lumens	6223
Material	Aluminum, Copper Free (less than 4/10 of 1%)
Operating Temperature Range Celcius	-20°C to +50°C
Series	VM4L
UPC	783936151786

Electrical Ratings

Lumens Per Watt	156
Voltage Rating	120-277 VAC
Wattage	40 W

Product Assets

[Customer Notices - Prop 65 Notice](#)



A proud member of the Hubbell Family.

