



## VML-X Series LED Area light 140 Watt, 120-277VAC, 18000 Lumen 1-1/2" 25° Stanchion Mount

By Killark  
Catalog # [VML2X1830D5G](#)



The VML-X Series is an Area Light fixture using energy efficient LED's. The redesigned CertiLite VML-X uses optics on the LED's to direct the light to where it is needed. This fixture is made with a cast copper-free aluminum housing and mount that is suitable for harsh and hazardous environments. The design of this fixture internal heat sink keeps a clean look on the outside of the fixture creating a LED fixture that does not contain external heat fins. Easily Retro fit any old HID or LED fixture to the new VML-X for a cleaner more efficient light.

### Features

- Energy Efficient and Long Life LED's
- Walkway Optic patterns
- Easy Retrofit to Competitors
- Finless Design
- Lighter Weight
- LED Color of 5000K with 80 CRI
- Wildlife Friendly Color options

### Application

- Class I Division 2 Hazardous Locations
- Class II Hazardous Dust
- Zone 2 Hazardous Locations
- Off and On Shore Oil and Gas
- Wet and Marine Locations
- Food and Beverage
- Heavy Industrial

### General

Color Temperature	5000 K
Finish Type	Powder Epoxy Paint
Light Source	LED
Lumen Range	12,000 - 18,000 lm
Lumens	18000
Mounting Type	25° Stanchion
Optic Type	Glass Globe
Series	VML-X

### Dimensions

Hub Size	1-1/2"
----------	--------

### Electrical Ratings

Current / Amperage Rating	1.17-0.51 A
Frequency Rating	50-60 Hz
Voltage Rating	120-277 VAC
Wattage	140 W

### Certifications and Compliance

Hazardous Rating(s)	<ul style="list-style-type: none"><li>• Class I, Div2, Groups A,B,C,D</li><li>• Class I, Zone 2, Groups IIC, IIB, IIA</li><li>• Class II, Div. 1&amp;2, Groups E,F,G</li><li>• IECEx QPS 15.0006</li><li>• Ex ec IIC T4/T3 Gc</li><li>• Ex tb IIIC T4/T3 Db</li><li>• QPS 22ATEX7000</li></ul>
---------------------	--

### Product Assets

[Brochures - VML-X Series Hazardous Location Luminaires Brochure](#)  
[Brochures - VML-X Series for Harsh and Hazardous Environments](#)  
[Catalog Page - VML-X Series Catalog Pages](#)  
[Certifications - VMLX/VM4L Series ATEX Certificate](#)  
[Certifications - VMLX Series QPS North American Certification](#)  
[Certifications - VMLX/VM4L Series EU Type ATEX Certificate](#)  
[Installation Manuals - VMLX Series IOM K1531](#)  
[Photometry - KIL\\_VML2X1830N](#)  
[Photometry - KIL\\_VML2X1830NAR](#)  
[Photometry - KIL\\_VML2X1830NDR](#)  
[Video - VML-X Features and Benefits](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
KILL-VML2X1830D5G-SPEC-EN | REV 7/2023

