



VML-X Series LED Area light 250 Watt, 120-277VAC, 28000 Lumen 1-1/4" 25° Stanchion Mount

By Killark
Catalog # [VML3X2830D4G](#)



The VML-X Series is an Area Light fixture using energy efficient LED's. The redesigned CertiLite VML-X uses optics on the LED's to direct the light to where it is needed. This fixture is made with a cast copper-free aluminum housing and mount that is suitable for harsh and hazardous environments. The design of this fixture internal heat sink keeps a clean look on the outside of the fixture creating a LED fixture that does not contain external heat fins. Easily Retro fit any old HID or LED fixture to the new VML-X for a cleaner more efficient light.

Features

- Energy Efficient and Long Life LED's
- Walkway Optic patterns
- Easy Retrofit to Competitors
- Lighter Weight
- LED Color of 5000K with 80 CRI
- Wildlife Friendly Color options

Application

- Class I Division 2 Hazardous Locations
- Class II Hazardous Dust
- Zone 2 Hazardous Locations
- Off and On Shore Oil and Gas
- Wet and Marine Locations
- Food and Beverage
- Heavy Industrial

General

Color Temperature	5000 K
Finish Type	Powder Epoxy Paint
Light Source	LED
Lumen Range	23,000 - 28,000 lm
Lumens	28000
Mounting Type	25° Stanchion
Optic Type	Glass Globe
Series	VML-X

Dimensions

Hub Size	1-1/4"
----------	--------

Electrical Ratings

Current / Amperage Rating	2.08-0.09 A
Frequency Rating	50-60 Hz
Voltage Rating	120-277 VAC
Wattage	250 W

Certifications and Compliance

Hazardous Rating(s)	<ul style="list-style-type: none">• Class I, Div2, Groups A,B,C,D• Class I, Zone 2, Groups IIC, IIB, IIA• Class II, Div. 1&2, Groups E,F,G• IECEx QPS 15.0006• Ex ec IIC T4/T3 Gc• Ex tb IIIC T4/T3 Db• QPS 22ATEX7000
---------------------	--

Product Assets

- [Brochures - VML-X Series Hazardous Location Luminaires Brochure](#)
- [Brochures - VML-X Series for Harsh and Hazardous Environments](#)
- [Catalog Page - VML-X Series Catalog Pages](#)
- [Certifications - VMLX/VM4L Series ATEX Certificate](#)
- [Certifications - VMLX Series QPS North American Certification](#)
- [Certifications - VMLX/VM4L Series EU Type ATEX Certificate](#)
- [Installation Manuals - VMLX Series IOM K1531](#)
- [Photometry - KIL_VML3X2830N](#)
- [Photometry - KIL_VML3X2830NDR](#)
- [Video - VML-X Features and Benefits](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
KILL-VML3X2830D4G-SPEC-EN | REV 7/2023