



## VML-X Series LED Area light 250 Watt, 120-277VAC, 28000 Lumen Driver Tank

By Killark

Catalog # [VML3X2830G](#)



The VML-X Series is an Area Light fixture using energy efficient LED's. The redesigned CertiLite VML-X uses optics on the LED's to direct the light to where it is needed. This fixture is made with a cast copper-free aluminum housing and mount that is suitable for harsh and hazardous environments. The design of this fixture internal heat sink keeps a clean look on the outside of the fixture creating a LED fixture that does not contain external heat fins. Easily Retro fit any old HID or LED fixture to the new VML-X for a cleaner more efficient light.

### Features

- Energy Efficient and Long Life LED's
- Walkway Optic patterns
- Easy Retrofit to Competitors
- Lighter Weight
- LED Color of 5000K with 80 CRI
- Wildlife Friendly Color options

### Application

Class I Division 2 Hazardous Locations  
Class II Hazardous Dust  
Zone 2 Hazardous Locations  
Off and On Shore Oil and Gas  
Wet and Marine Locations  
Food and Beverage  
Heavy Industrial

### General

|                   |                    |
|-------------------|--------------------|
| Catalog Number    | VML3X2830G         |
| Color Temperature | 5000 K             |
| Finish Type       | Powder Epoxy Paint |
| Light Source      | LED                |
| Lumen Range       | 23,000 - 28,000 lm |
| Lumens            | 28000              |
| Optic Type        | Glass Globe        |
| Series            | VML-X              |
| UPC               | 783936185460       |

### Electrical Ratings

|                           |             |
|---------------------------|-------------|
| Current / Amperage Rating | 2.08-0.09 A |
|---------------------------|-------------|

|                  |             |
|------------------|-------------|
| Frequency Rating | 50/60 Hz    |
| Voltage Rating   | 120-277 VAC |
| Wattage          | 250 W       |

### Certifications And Compliance

|                     |   |
|---------------------|---|
| Hazardous Rating(s) | <ul style="list-style-type: none"><li>• Class I, Div2, Groups A,B,C,D</li><li>• Class I, Zone 2, Groups IIC, IIB, IIA</li><li>• Class II, Div. 1&amp;2, Groups E,F,G</li><li>• IECEx QPS 15.0006</li><li>• Ex ec IIC T4/T3 Gc</li><li>• Ex tb IIIC T4/T3 Db</li><li>• QPS22ATEX7000</li></ul> |
|---------------------|---|

### Product Assets

[Brochures - VML-X Series for Harsh and Hazardous Environments](#)

[Certifications - VMLX/VM4L Series ATEX Certificate](#)

[Certifications - VMLX/VM4L Series EU Type ATEX Certificate](#)

[Certifications - VMLX & VM4L Series Attestation of Conformity](#)

[Certifications - VMLX Series QPS North American Certification](#)

[Certifications - VMLX & VM4L Series IECEx Certification](#)

[Installation Manuals - VMLX Series IOM K1531](#)

[Photometry - KIL\\_VML3X2830NDR](#)

[Photometry - KIL\\_VML3X2830N](#)

[Specifications - VML3X2830G](#)

[Video - VML-X Features and Benefits](#)



A Hubbell brand

©2025 Hubbell Incorporated. All rights reserved  
KILL-VML3X2830G-SPEC-EN | REV 3/2025