



35 kV Class Large Interface Elbow Arrester (27 kV MCOV)

By Hubbell
Catalog # [236ELA33](#)

ELBOW ARRESTER, 35KV 27 MCOV, Mates with IEEE Std. 386, Interface 9



*Representative Image

Features

- Meets or Exceeds IEEE Std. 386 and IEEE Std. C62.11. Section 8.1 requirements
- Interchangeable with other products meeting the same requirements
- Fully shielded, insulated and submersible

General

| | |
|-----------------|-----------------------|
| Grounding Style | 36 in Line Lead |
| Type | Underground Arresters |
| UPC | 096359801122 |

Electrical Ratings

| | |
|---|-------------------|
| Duty Cycle | 33 kV |
| MCOV | 26.9 kV |
| Maximum Discharge Voltage | 107.6 kV @ 1.5 kA |
| | 92.2 kV @ 3 kA |
| | 98.3 kV @ 5 kA |
| | 110.7 kV @ 10 kA |
| | 127.9 kV @ 20 kA |
| | 159.8 kV @ 40 kA |
| Maximum Switching Surge Protective Level @ 500A | 77.5 kV |
| kV Class | 35 kV |

Logistics

| | |
|------------------|----|
| Pallet Quantity | 64 |
| Standard Package | 1 |

Product Assets

- [Catalogs - Cable Accessories](#)
- [Catalogs - Underground Arresters](#)
- [Literature - Application Guide: Metal-oxide Surge Arresters for use on AC systems](#)
- [Sales Drawings - 35 kV, 200A Large interface Loadbreak Elbow Arrester](#)
- [Video - Grease Best PRactices](#)
- [Video - Hubbell Power Systems Metal Oxide Varistor](#)



A Hubbell brand