



B7CA - B7C Series, Aluminum Circuit Breaker Enclosure, 100A Max

By Killark
Catalog # B7CA

B7C Series- Aluminum Circuit Breaker Enclosure- 100A Max.



General

Actuator	Molded Case Circuit Breaker Operator
Application	
Catalog Number	B7CA
Color	Aluminum Aluminium
EU RoHS Indicator	Contact Manufacturer
Enclosure Type	Bolted
Finish Type	Laque
Material	Aluminum, Copper Free (less than 4/10 of 1%)
Mounting Type	
Operating Temperature Celcius Max	40 Degree
Series	B7C
Type	
UPC	783936015040

Dimensions

Depth	9.125
Gross Weight with Packaging	46
Height	18 in
Weight	46 lb
Width	11 in

Electrical Ratings

Frequency Rating	60 Hz
------------------	-------

Certifications And Compliance

CSA File Number	LR11714
Hazardous Rating(s)	Class I, Divisions 1 & 2, Groups B, C, D Class I, Zones 1 & 2, Groups IIB+H2, IIA Class II, Divisions 1 & 2, Groups E, F, G Class III, Divisions 1 & 2
Nema Rating	3, 4, 4X, 7(B, C, D), 9(E, F, G)
UL File Number	E83969

Product Assets

- [3D Models - B7CA 3D File](#)
- [Catalogs - Killark Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Engineering Drawing - B7CA Engineering Drawing](#)
- [Installation Manuals - Ground Lugs IOM K0974](#)
- [Installation Manuals - KIL_B7CA Series Mounting Pan IOM_K1158](#)
- [Sales Drawings - B7CA Sales Drawing](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
KILL_CA-B7CA-SPEC-EN | REV 6/2024