



35 kV, Load Break Elbow w/ Bimetal Contact

By Hubbell
Catalog # [236LE55](#)

Load Break Elbow, 200 Amp, 35 kV, Long Bimetal Contact,
Cable Insulation Diameter range = 1.020 - 1.310 inches, 2/0 Solid
or Compacted and 1/0 Stranded or Compressed



*Representative Image

Features

- Meets or Exceeds IEEE Std. 386 and IEEE Std. 592 requirements
- Interchangeable with other products meeting the same requirements
- Fully shielded, insulated and submersible
- Optional features include test point, integral seal, cold shrink jacket seal kit or shield adapter kit

General

Catalog Number	236LE55
Connector Type	Bi-Metal
EU RoHS Indicator	No
PROBELOK ? Connectors	No
Type	200Amp Load Break
UPC	096359530879
With Seal Kit	No
With Test Point	No

Dimensions

Cable Insulation Diameter Maximum	1.31 in
Cable Insulation Diameter Minimum	1.02 in
Dimensions	12.250 in x 12.00 in x 5.00 in
Height	5 in
Length	12.25 in
Weight	5.5 lb
Width	12 in

Electrical Ratings

AC Withstand Voltage (1 min)	50 kV
Basic Impulse Level	150 kV
Corona Extinction (3pC)	26 kV
Current Rating	200 A
kV Class	Large Interface 35 kV

Conductor Related

Cable Insulation Diameter Range	1.020 - 1.310
Solid or Compacted Conductor	2/0
Stranded or Compressed Conductor	1/0

Logistics

Carton Quantity	9
Pallet Quantity	108
Standard Package	20

Product Assets

- [Catalogs - Cable Accessories](#)
- [Installation Manuals - Recommended Crimp Tools and Dies for 200A Elbow Bi-Metal Connectors](#)
- [Installation Manuals - Loadbreak Connector 200A, 35kV Class Elbow](#)
- [Literature - Loadbreak Elbow Infographic](#)
- [Sales Drawings - Elbow, 200A 35 KV size 5](#)
- [SDS - VERSILUBE G661 SILICONE COMPOUND](#)
- [Test Documents - Separable Connectors 35kV 200 A](#)
- [Video - Grease Best PRactices](#)
- [Video - 200A Loadbreak Elbow Fault Closure](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
HubbellBrand-236LE55-SPEC-EN | REV 6/2024