

**Cable Adapter with Cable Insulation**  
**Diameter Range = 0.760 - 0.950**  
**inches**

By Hubbell Power Systems  
Catalog # [625CAG](#)



15/25/28 kV 600/900 Amp Cable Adapter, Cable Insulation  
Diameter Range = 0.760 - 0.950 inches

**Features**

- Meets or Exceeds IEEE Std. 386 and IEEE Std. 592 requirements
- Interchangeable with other products meeting the same requirements
- Tapered design

**General**

Catalog Number	625CAG
EU RoHS Indicator	No
Type	600 Amp Dead Break
UPC	096359393061

**Dimensions**

Cable Insulation Diameter Maximum	0.95 in
Cable Insulation Diameter Minimum	0.76 in
Weight	1 lb

**Electrical Ratings**

AC Withstand Voltage (1 min)	45 kV
------------------------------	-------

Basic Impulse Level	125 kV
Corona Extinction (3pC)	21 kV
Current Rating	600 A
Voltage Rating	15 kV

**Conductor Related**

Cable Insulation Diameter Range	0.760 - 0.950
------------------------------------	---------------

**Certifications And Compliance**

Buy America(n) Qualified	TAA Compliant (All status valid till December 2024)
--------------------------	--

**Logistics**

Standard Package	1
------------------	---

**Product Assets**

- [Catalogs - Cable Accessories](#)
- [Sales Drawings - 625CA](#)
- [SDS - VERSILUBE G661 SILICONE COMPOUND](#)
- [Specifications - 625CAG](#)
- [Video - Grease Best PRactices](#)