

HC14192626502, Type 712 Switch Module

By Hubbell Industrial Controls (ICD)

Catalog # [HC14192626502](#)

TYPE 712 SWITCH MODULE, DPDT NON-INTERRUPTING, 1500 VOLTS DC, 1600 AMPS, WITHOUT MOTOR CUTOFF ASSEMBLY

Features

- Two-Pole Double-Throw Non-interrupting Switch
- 1600 Amp 1500 VDC rating
- Motor Cut-Out (MCO) option
- Trifurcated main contacts
- Silver alloy main contacts
- Silver-plated current-carrying connections
- High dielectric and mechanical strength

General

Catalog Number HC14192626502



Maximum interrupting capacity 100 A
Through current capability 30000

Electrical Ratings

Maximum Current Rating Amps 1600 Amps @ 40°C ambient
Continuous

Product Assets

[Catalogs - 100D DC Devices Brochure](#)

[Catalogs - 42711/42712 Motor Operated Switch Catalog](#)

[Specifications - HC14192626502](#)



A Hubbell brand