



ESXC120AA2G

By Killark
Catalog # [ESXC120AA2G](#)

Class I 120V, Clear Strobe, 3/4" Pendant with Guard.



Features

- Electronic component temperature range -40°C to +55°C
- NEC temperature code, T6 (<85°C)
- Flash rate-85 flashes per minute
- Xenon type lamp
- Voltage and amperage: 12-74 VDC: Draws 1.25A avg. @ 12 VDC tapering to 0.2A avg. @ 74 VDC, .75A avg. @ 24 VDC
- 120 VAC (50/60 HZ): Draws 0.30A avg.
- 240 VAC (50/60 HZ): Draws 0.17A avg.
- Power supply output: 13 watts standard 11 watts for 12-74 VDC

General

Finish Type	Peinture époxy en poudre
Lamp Type	Flashing
Light Source	Xenon
Material	Aluminum, Copper Free (less than 4/10 of 1%)
Mounting Type	Pendant
Optic Type	Polycarbonate Lens - Clear
Series	ESX
UPC	783936028590

Dimensions

Hub Size	3/4"
----------	------

Electrical Ratings

Frequency Rating	50/60 Hz
Voltage Rating	120 VAC

Certifications and Compliance

Hazardous Rating(s)	<ul style="list-style-type: none">• Class I, Divisions 1 & 2, Groups C, D• Class I, Zones 1 & 2, Groups IIB, IIA• Class II, Divisions 1 & 2, Groups E, F, G• Class III, Divisions 1 & 2
---------------------	--

Logistics

Carton Quantity	1
-----------------	---

Product Assets

[Certifications - ESX Series UL Certification](#)
[Customer Notices - Prop 65 Notice](#)
[Installation Manuals - KIL_ESX Series Signal Luminaire IOM_K1121](#)



A proud member of the Hubbell Family.