

**HC91814202 MAGNET
CONTROLLER 4295 SIZE 2**

By Hubbell Industrial Controls (ICD)
Catalog # [HC91814202](#)



TYPE 4295 LIFTING MAGNET CONTROLLER, AUTOMATIC
DISCHARGE RESISTOR, 25-50 AMPS COLD MAGNET CURRENT,
230 VOLTS DC, NEMA 1A/3R ENCLOSED

Features

- Front-Wired Front-Removable components. Mechanically interlocked "LIFT" and "DROP" contactors.
- Permanently connected discharge path completely independent from the line.
- High-Thermal capacity resistor discharge path.
- Peak magnet induced voltage limited to under 900 volts.
- Long electrical contact life. Minimum Maintenance. Dribble feature - Standard.
- Ventilated NEMA 3R Enclosure. 13 to 175 Amps cold magnet current.
- Mechanically rugged high thermal capacity discharge resistor.
- Permanently connected discharge path completely independent of the line.
- Mechanically interlocked Lift and Drop contactors.

General

Catalog Number	HC91814202
Series	4295 Euclid
Type	Automatic Discharge

Dimensions

Dimensions	16.12 in x 10 in x 24.25 in
Height	24.25 in
Length	16.12 in
Width	10 in

Electrical Ratings

Current / Amperage Rating	25-50 A
---------------------------	---------

Certifications And Compliance

Contactor NEMA Rating	2
Enclosure NEMA Rating	1A/3R
Nema Rating	NEMA 2

Product Assets

[Catalogs - 100E Euclid Brochure](#)
[Installation Manuals - ICD_4291Pub180_CATALOG](#)
[Specifications - HC91814202](#)