



EXH Series CB Handle,4 Pole 400 Amp Frame Breaker In 10" Deep Boxes Class I, II, III, CDEFG, UL/CSA, 316 SS Shaft, Cast Alum Handle Type 4X IP66

By Killark
Catalog # [EXH2C10](#)



*Representative Image

EXH Series,4 Pole 400 Amp Frame Breaker In 10" Deep Boxes Class I, II, III, CDEFG, UL/CSA, 316 SS Shaft, Cast Alum Handle Type 4X IP66, Circuit Breaker Handle

Features

- Circuit breaker handle.
- Factory or field installed in a 3/4" NPSM opening.
- Has provision for Lock-On and Lock-Off with up to three padlocks.
- Consists of an external handle mechanism with through-the-enclosure shaft, internal toggle mechanism, and universal breaker pan.
- Copper free aluminum with 316 stainless steel shaft and sprongs.
- O-ring 70 durometer nitrile.
- Extruded aluminum bodies, stainless steel pins and stainless steel hardware.

General

Catalog Number	EXH2C10
Color	Gray
EU RoHS Indicator	Contact Manufacturer
Material	Copper-free aluminum
Series	EXH
UPC	783936118567

Dimensions

Gross Weight with Packaging 4.5

Certifications And Compliance

CSA File Number	LR11714
Hazardous Rating(s)	<ul style="list-style-type: none">• Class I, Divisions 1 & 2, Groups B, C, D• Class I, Zones 1 & 2, Groups IIB+H2, IIA• Class II, Divisions 1 & 2, Groups E, F, G• Class III, Divisions 1 & 2
Nema Rating	3, 4, 4X
UL File Number	E150827

Product Assets

- [Catalogs - Killark Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Specifications - EXH2C10](#)
- [Specifications - EXH2C10 Specification Sheet French](#)
- [Specifications - EXH Series Circuit Breaker Handles Specification Sheet](#)