



HKH Series Control Station, Double Pilot Lights Red and Green- Stainless Steel 1b- Panel Mount - M20

By Killark
Catalog # [HKH1BEPALRLOLGLO](#)

HKH Double Pilot Lights Red and Green- Stainless Steel 1b- Panel Mount - M20



Features

- Size 1 Control Stations available as 1a, 1b, & 1c as standard catalog number offerings for 1, 2 & 3 device openings and will accept 2-M20 entries in either end.
- Ammeters available in 1b & 1c.
- Size 2 Enclosures available as 2a & 2c for 2, 4 & 6 device entries in cover with ability to accept 2-M25 entries in either end.
- Operating Temperature of -50°C to +60°C.
- Explosion Protected contact blocks 690 VAC N.O. & N.C. capable of 20 Amps for Switching Duty and HP Ratings up to 1HP.
- LED Pilot Light modules for 12-250V AC/ DC for UL applications. 12-254V AC/DC for IEC applications.
- Contacts & Pilot lights can be mounted inside enclosure on Din Rail or in cover to the actuator.
- Accessories available for Lockout/Tag Out functions made in 316 stainless steel.

Application

Hazardous and corrosive environments due to the presence of flammable gases or vapors, combustible dusts or ignitable fiber or flyings, Installations at petroleum refineries, chemical and petrochemical plants and other processing or storage facilities where similar hazards exist, Use in conjunction with motor starters or contactors for remote control of motors

General

Actuator	Double Pilot Light
Ambient Temp. Range	-50 °C to 60 °C
Color	Red-Green
EU RoHS Indicator	Contact Manufacturer
Material	Stainless Steel, Type 316
Mounting Type	Wall
Operating Temperature Range Celcius	-50°C to 60°C
Series	HKH
UPC	783936128047

Dimensions

Depth	4.16
Hub Size	3/4"
Weight	1.66 lb

Electrical Ratings

Amperage Rating	0.05 A
-----------------	--------

Certifications and Compliance

ATEX File Number	1405X
Hazardous Rating(s)	<ul style="list-style-type: none"> • Class I, Division 2, Groups A, B, C, D • Class II, Division 1, Groups E, F, G (Canada Only) • Class II, Division 2, Groups E, F, G • Class III, Divisions 1 & 2 • Zones 1 & 2 • Zones 21 & 22
IECEX File Number	15.0054X
Nema Rating	3, 4, 4X, 12, 13
UL File Number	E53360

Product Assets

- [3D Models - KIL_HKH1BEPALRLOLGLO](#)
- [Brochures - HKH Brochure](#)
- [Certifications - HKH Series E-Stop Assemblies Attestation of Conformity](#)
- [Certifications - HKH Series Control Stations IECEx Certification](#)
- [Certifications - HKH Inmetro Certificate of Conformity](#)
- [Certifications - HKH Series Control Stations ATEX Certificate](#)
- [Certifications - HKH Series Control Stations UL Certification](#)
- [Certifications - HKH Series Actuators, Pilotlights, & Plugs Declaration of Conformity](#)
- [Certifications - HKH Series Control Stations Declaration of Conformity](#)
- [Certifications - HKH Series Control Stations UKCA Certificate](#)
- [Customer Notices - Prop 65 Notice](#)
- [Installation Manuals - HKH Series Control Stations Installation Manual K1466](#)
- [Sales Drawings - HKH1BEPALRLOLGLO Sales Drawing \(PDF\)](#)

Amperage Rating
Frequency Rating

0.05 A
50/60 Hz



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
KILL-HKHIBEPALROLGLO-SPEC-EN | REV 7/2023